





### Series Fan Powered Air Terminal Unit



The standard location for control enclosure is Left Hand. Looking in the direction of airflow, the control enclosure is on the left.

Case size 7 includes two discharge blowers.

All dimensions shown in inches, parentheses ( ) indicate millimeters.

For use with 4" Transitions on standard 6" Inlet Duct

\* 10" Length for 4" Inlet \*

PSC MOTOR CONFIGURATION					
Case Size	Horse Power	Discharge			
		Loc.	Width	Height	
		C	D	E	
2	1/8	10 15/16 (278)	8 3/8 (213)	10 1/8 (257)	
3	1/8	12 3/16 (309)	11 15/16 (303)	7 3/4 (197)	
4	1/4	11 1/2 (292)	13 1/4 (336)	10 1/8 (257)	
5	1/3	13 1/2 (343)	13 1/4 (336)	11 3/16 (284)	
6	1	14 1/8 (359)	14 (355)	13 1/2 (343)	
7	3/4 (QTY 2)	5 13/16 (148)	13 1/4 (337)	9 1/2 (241)	

Case Size	Inlet Size		Unit Width W	Unit Height H	Unit Length L	Induction	
	Standard	Optional				Width A	Height B
2	8 (203)	4,5,6,10,12	30 (762)	17 1/2 (445)	36 (914)	14 (356)	14 (356)
3	10 (254)	4,5,6,8,12,14	36 (914)	17 1/2 (445)	40 (1016)	18 (457)	14 (356)
4	12 (305)	8,10,14	36 (914)	17 1/2 (445)	40 (1016)	18 (457)	14 (356)
5	14 (356)	10,12,16	40 (1016)	20 (508)	40 (1016)	18 (457)	16 (406)
6	16 (406)	10,12,14	42 (1067)	20 (508)	42 (1067)	20 (508)	16 (406)
7	16 (406)	12,14,18x16	46 (1168)	20 (508)	46 (1168)	22 (559)	16 (406)

ECM MOTOR CONFIGURATION					
Case Size	Horse Power	Discharge			
		Loc.	Width	Height	
		C	D	E	
2	1/3	9 1/8 (231)	11 15/16 (303)	7 3/4 (197)	
3	1/3	12 3/16 (309)	11 15/16 (303)	7 3/4 (197)	
4	1/2	12 3/4 (324)	10 5/8 (270)	10 7/8 (276)	
5	1	13 1/2 (343)	13 1/4 (336)	11 3/16 (284)	
6	1	14 1/8 (359)	14 (355)	13 1/2 (343)	
7	1 (QTY 2)	5 13/16 (148)	13 1/4 (337)	9 1/2 (241)	

Standard Construction		
<ul style="list-style-type: none"> <li>1" Dual Density, Coated Fiberglass</li> <li>All Insulations Meet NFPA 90A And UL 181</li> <li>All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration</li> </ul>	<ul style="list-style-type: none"> <li>Units Are Constructed With 20 Gauge Casing, 20 Gauge Inlet Duct, and 18 Gauge Discharge.</li> <li>18 Gauge Equivalent Damper Assembly With Integral Blade Seal</li> <li>32 x 12 Control Enclosure</li> </ul>	<ul style="list-style-type: none"> <li>Optional Flanged Slip &amp; Drive Discharge Connection</li> <li>Optional Induction Attenuator</li> <li>Inlet Airflow Sensor</li> </ul>