



Series Fan Powered Air Terminal Unit  
With Electric Heat



For use with 4" Transitions on standard 6" Inlet Duct

\* 10" Length for 4" Inlet \*

The standard location for control enclosure is Left Hand. Looking in the direction of airflow, the control enclosure is on the left.

Case size 7 includes two discharge blowers.

Case Size	Inlet Size		Horse Power		Unit Width W	Unit Height H	Unit Length L	Induction		Discharge		
	Standard	Optional	PSC	ECM				Width A	Height B	Loc. C	Width D	Height E
2	8 (203)	4,5,6,10,12	1/8	1/3	30 (762)	17 1/2 (445)	36 (914)	14 (356)	14 (356)	7 (178)	16 (406)	15 (381)
3	10 (254)	4,5,6,8,12,14	1/8	1/3	36 (914)	17 1/2 (445)	40 (1016)	18 (457)	14 (356)	10 (254)	16 (406)	15 (381)
4	12 (305)	8,10,14	1/4	1/2	36 (914)	17 1/2 (445)	40 (1016)	18 (457)	14 (356)	8 (203)	20 (508)	17 1/2 (445)
5	14 (356)	10,12,16	1/3	1	40 (1016)	20 (508)	40 (1016)	18 (457)	16 (406)	10 (254)	20 (508)	17 1/2 (445)
6	16 (406)	10,12,14	1	1	42 (1067)	20 (508)	42 (1067)	20 (508)	16 (406)	10 (254)	20 (508)	17 1/2 (445)
7	16 (406)	12,14,18x16	3/4 (QTY 2)	1 (QTY 2)	46 (1168)	20 (508)	46 (1168)	22 (559)	16 (406)	4 (102)	38 (965)	20 (508)

**Standard Construction**

- 1" Dual Density, Coated Fiberglass
- All Insulations Meet NFPA 90A And UL 181
- All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration
- Units Are Constructed With 20 Gauge Casing, 20 Gauge Inlet Duct, and 18 Gauge Discharge.
- 18 Gauge Equivalent Damper Assembly With Integral Blade Seal
- 32 x 12 Control Enclosure
- Slip & Drive Discharge Connection
- Optional Electric Heat Access Door
- Optional Induction Attenuator
- Inlet Airflow Sensor