



## Low Profile Series Fan Powered Air Terminal Unit With Hot Water Coil



Inlet View Case Size 2

Top View Case Size 2

Discharge View Case Size 2



Inlet View Case Size 4


Top View Case Size 4

Discharge View Case Size 4

The standard location for control enclosure is Left Hand. Looking in the direction of airflow, the control enclosure is on the left.

Case size 4 includes two discharge blowers

All Dimensions shown in inches, parentheses ( ) indicate millimeter



Optional Inlet Sizes 4,5 and 6. Available On Case Size 2 Only

Case Size	Inlet Size Standard	Unit Width W	Unit Length L	Unit Height H	Induction		Discharge		PSC MOTOR CONFIGURATION	
					Width A	Height B	Width C	Height D	Case Size	Horse Power
2	8 (203) Round	23 (584)	39 (991)	11 (279)	10 1/2 (267)	8 1/2 (216)	22 (559)	10 1/2 (267)	2	1/4
4	8 (203) x 16 (406) Rect.	42 (1067)	39 (991)	11 (279)	18 (457)	8 1/2 (216)	32 (813)	10 1/2 (267)	4	1/4 (QTY 2)

ECM MOTOR CONFIGURATION	
Case Size	Horse Power
2	1/3
4	1/3 (QTY 2)

### Standard Construction

- 1/2" Dual Density, Coated Fiberglass
- All Insulations Meet NFPA 90A And UL181
- All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration
- Units Are Constructed With 22 Gauge Casing and 18 Gauge Discharge
- 18 Gauge Equivalent Damper Assembly with Integral Blade Seal
- 18 x 10 Control Enclosure
- Slip & Drive Discharge Connection
- Optional Induction Attenuator
- Inlet Flow Sensor