

SERIES XG-SGRP PERFORMANCE DATA
MODEL XG-SGRP

Size (in)	NK Vel	100	150	200	250	300	350	400	450	500	600	700
Neck Area ft ²	Ps	.002	.004	.008	.012	.018	.024	.032	.040	.049	.071	.096
06x06 .250	CFM	25	38	50	63	75	88	100	113	125	150	175
	Throws	1-5	2-7	3-10	4-12	5-13	6-15	6-16	7-17	8-17	10-19	11-21
	NC	-	-	-	-	11	15	19	23	26	31	36
08x06 .333	CFM	34	50	67	84	100	117	134	150	167	200	234
	Throws	1-5	2-8	4-11	5-14	6-16	6-17	7-18	8-19	9-20	11-22	13-24
	NC	-	-	-	-	12	16	20	24	27	33	37
08x08 .444	CFM	45	67	89	111	134	156	178	200	222	267	311
	Throws	1-6	3-9	4-13	5-16	6-18	7-19	8-21	10-22	11-23	13-25	15-27
	NC	-	-	-	-	13	18	22	25	26	34	38
09x06 .375	CFM	38	57	75	94	113	132	150	169	188	225	263
	Throws	1-6	3-9	4-12	5-15	6-17	7-18	8-19	9-20	10-21	12-23	14-25
	NC	-	-	-	-	12	17	21	25	28	33	38
09x09 .563	CFM	57	85	113	141	169	198	226	254	282	338	395
	Throws	1-7	3-11	5-14	6-18	7-20	8-22	10-23	11-25	12-26	14-29	17-31
	NC	-	-	-	-	14	19	23	26	29	35	39
10x06 .417	CFM	42	63	84	105	126	146	167	188	209	251	292
	Throws	1-6	3-9	4-12	5-15	6-17	7-19	8-20	9-21	10-22	12-25	14-27
	NC	-	-	-	-	13	18	21	25	28	34	38
10x08 .556	CFM	56	84	112	139	167	195	223	251	278	334	390
	Throws	1-7	3-11	5-14	6-18	7-20	8-22	9-23	11-25	12-26	14-28	17-31
	NC	-	-	-	-	14	19	23	26	29	35	39
10x10 .694	CFM	70	105	139	174	209	243	278	313	347	417	486
	Throws	1-8	3-12	5-16	7-20	8-22	9-24	11-26	12-27	13-29	16-32	19-34
	NC	-	-	-	-	15	20	24	27	30	36	40
12x06 .500	CFM	50	75	100	125	150	175	200	225	250	300	350
	Throws	1-7	3-10	5-14	6-17	7-19	8-21	9-22	10-21	11-25	14-27	16-29
	NC	-	-	-	-	14	18	22	26	29	34	39
12x08 .667	CFM	67	101	134	167	201	234	267	301	334	401	467
	Throws	1-8	3-12	5-16	7-20	8-22	9-24	10-25	12-27	13-28	16-31	18-34
	NC	-	-	-	-	15	20	23	27	30	36	40
12x10 .833	CFM	84	125	167	209	250	292	334	375	417	500	584
	Throws	2-9	4-13	6-17	7-12	9-25	10-27	12-28	13-30	15-32	17-35	20-38
	NC	-	-	-	-	16	20	24	28	31	37	41
12x12 1.000	CFM	100	150	200	250	300	350	400	450	500	600	700
	Throws	2-10	4-14	6-19	8-24	10-27	11-29	13-31	14-33	16-35	19-38	22-41
	NC	-	-	-	11	17	21	25	29	32	37	42

SERIES XG-SGRP PERFORMANCE DATA
MODEL XG-SGRP

Size (in)	Nk Vel	100	150	200	250	300	350	400	450	500	600	700
Neck Area ft ²	Ps	.002	.004	.008	.012	.018	.024	.032	.040	.049	.071	.096
14x08 .778	CFM	78	117	156	195	234	273	312	351	389	467	545
	Throws	2-8	4-13	6-17	7-21	8-24	10-26	11-27	13-29	14-31	17-34	20-36
	NC	-	-	-	-	16	20	24	28	31	36	41
14x14 1.361	CFM	137	205	273	341	409	477	545	613	681	817	953
	Throws	2-11	5-17	7-22	9-28	11-31	13-34	15-36	17-39	19-41	22-44	27-49
	NC	-	-	-	12	18	23	27	30	33	39	44
15x15 1.563	CFM	157	235	313	391	469	548	626	704	782	938	1095
	Throws	2-12	5-18	8-24	10-30	12-34	14-36	16-39	18-41	20-44	24-48	28-51
	NC	-	-	-	13	19	23	27	31	34	39	44
16x10 1.111	CFM	112	167	223	278	334	389	445	500	556	667	778
	Throws	2-10	4-15	7-20	8-25	10-28	12-31	13-33	15-35	17-37	20-40	23-43
	NC	-	-	-	12	17	22	26	29	32	38	42
16x12 1.333	CFM	134	200	267	334	400	467	534	600	667	800	934
	Throws	2-11	5-17	7-22	9-28	11-31	13-34	15-36	17-38	18-40	22-44	26-48
	NC	-	-	-	12	18	22	26	30	33	39	43
16x16 1.778	CFM	178	267	356	445	534	623	712	801	889	1067	1245
	Throws	2-13	5-19	8-25	11-32	13-36	15-39	17-41	19-44	21-46	25-51	30-55
	NC	-	-	-	14	19	24	28	31	34	40	44

PERFORMANCE NOTES FOR SERIES XG-SGRP

All data is tested in accordance with ANSI/ASHRAE 70-2006.

DEFINITION OF UNITS

CFM Cubic Feet per Minute (air)

Nk Vel Neck Velocity is the airstream velocity in the duct just before it reaches the supply outlet; measured in Feet per Minute

NC Noise criterion, sound pressure level NC ratings are based on sound power level (Lw) re: 10⁻¹² watts minus a 10dB room attenuation in all octave bands

Throw Throw distance in feet are for terminal velocities of 50 and 100fpm respectively

Ps Static pressure = Pt-Pv (inches of water column)