


Square Retrofit Air Terminal



Standard Construction		
<ul style="list-style-type: none"> • 1/2" Dual Density, Coated Fiberglass • All Insulations Meet NFPA 90A And UL 181 • All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration 	<ul style="list-style-type: none"> • Units Are Constructed With 20 Gauge Frame & 18 Gauge Damper Blade(s) 	<ul style="list-style-type: none"> • Inlet Airflow Sensor • Control Panel with Dust Cover



Submittal: XG-SR502B-001

Square Retrofit Air Terminal

CFM RANGE	AVAILABLE DUCT SIZES (inches)	
	Width W	Height H
0 to 200	6 8 10 12 - 8 10 12 - - 10 12	6 8 10
0 to 350	6 8 10 12 14 - 8 10 12 14 - - 10 12 14	6 8 10
0 to 500	8 10 12 14 16 8 10 12 14 16 - 10 12 14 16	6 8 10
0 to 875	10 12 14 16 18 10 12 14 16 18 - 12 14 16 18	8 10 12
0 to 1250	14 16 18 20 22 24 14 16 18 20 22 24 14 16 18 20 22 24	8 10 12
0 to 1400	12 14 16 18 20 22 12 14 16 18 20 22 - 14 16 18 20 22	10 12 14
0 to 1900	18 20 22 24 26 28 30 18 20 22 24 26 28 30 18 20 22 24 26 28 30	10 12 14
0 to 2400	18 20 22 24 26 28 30 18 20 22 24 26 28 30 18 20 22 24 26 28 30	12 14 16
0 to 3800	20 22 24 26 28 30 20 22 24 26 28 30 20 22 24 26 28 30	14 16 18
0 to 5400	22 24 26 28 30 32 34 36 22 24 26 28 30 32 34 36 22 24 26 28 30 32 34 36	16 18 20
0 to 6700	24 26 28 30 32 34 36 24 26 28 30 32 34 36 24 26 28 30 32 34 36	20 24 26
0 to 10000	30 32 34 36 38 40 42 44 46 30 32 34 36 38 40 42 44 46 30 32 34 36 38 40 42 44 46	20 24 26
0 to 15000	40 42 44 46 48 50 52 40 42 44 46 48 50 52 40 42 44 46 48 50 52	20 24 26