


**Low Profile Single Duct Air Terminal Unit
With Hot Water Coil**



The standard location for control panel is Right Hand on Low Profile Single Duct Air Terminal Unit With Water Coil. Looking in the direction of airflow, the control panel is on the right.

The control panel will overhang the top and bottom of Unit Sizes 4 - 6 1" [25.4 mm] or 13/16" [21 mm] on Unit Size 8 Control Panel Mounting Surface width by height is 13 7/8" x 9 3/4"

Unit Sizes 12, 14, & 16 Have Flat Oval Inlet Ducts

Unit Size	Inlet Size		A		Width		Height		Unit Weight.							
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	1 Row		2 Row		3 Row		4 Row	
									lb.	kg.	lb.	kg.	lb.	kg.	lb.	kg.
4	3 7/8	99	10	254	12	305	8	203	16.50	8	17.50	8	20.00	9	20.25	9
5	4 7/8	124	5	127	12	305	8	203	16.50	8	17.50	8	20.00	9	20.25	9
6	5 7/8	149	5	127	12	305	8	203	16.50	8	17.50	8	20.00	9	20.25	9
7	6 7/8	175	5	127	12	305	10	254	20.00	9	22.75	10	26.25	12	26.50	12
8	7 7/8	200	5	127	12	305	10	254	20.00	9	22.75	10	26.25	12	26.50	12
9	8 7/8	226	5	127	14	356	12 1/2	318	24.50	11	27.50	13	33.75	15	34.75	16
10	9 7/8	251	5	127	14	356	12 1/2	318	24.50	11	27.50	13	33.75	15	34.75	16
12	13 x 9 7/8	330 x 251	5	127	18	457	12 1/2	318	31.50	14	35.50	16	42.25	19	44.50	20
14	16 1/4 x 9 7/8	413 x 251	5	127	24	610	12 1/2	318	35.00	16	41.50	19	50.00	23	51.75	24
16	19 3/8 x 9 7/8	492 x 251	5	127	28	711	12 1/2	318	41.50	19	47.25	21	55.25	25	58.50	27

Standard Construction

- | | | |
|---|--|---|
| <ul style="list-style-type: none"> • 1/2" Dual Density, Coated Fiberglass • All Insulations Meet NFPA 90A And UL 181 • All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration | <ul style="list-style-type: none"> • Units Are Constructed With 22 Gauge Casing & Inlet Duct • 18 Gauge Equivalent Damper Assembly With Integral Blade Seal • Control Panel With Dust Cover | <ul style="list-style-type: none"> • Slip & Drive Discharge Connection • Inlet Airflow Sensor |
|---|--|---|