


**Low Profile Single Duct Air Terminal Unit  
With Integral Attenuator**




The standard location for control panel is Right Hand on Low Profile Single Duct Air Terminal Unit With Integral Attenuator. Looking in the direction of airflow, the control panel is on the right.

The control panel will overhang the top and bottom of Unit Sizes 4 - 6 1" [25 mm] or 1 3/16" [21 mm] on Unit Size 8 Control Panel Mounting Surface width by height is 13 7/8" x 9 3/4"

Unit Sizes	Nominal Size		A		Width		Height		Unit wt.	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	lb.	kg.
4	3 7/8	99	10	254	12	305	8	203	24	11
5	4 7/8	124	5	127	12	305	8	203	24	11
6	5 7/8	149	5	127	12	305	8	203	24	11
7	6 7/8	175	5	127	12	305	10	254	28	13
8	7 7/8	200	5	127	12	305	10	254	28	13
9	8 7/8	226	5	127	14	356	12 1/2	318	34	15
10	9 7/8	251	5	127	14	356	12 1/2	318	34	15
12	13 x 9 7/8	330 x 251	5	127	16	406	12 1/2	318	38	17
14	16 1/4 x 9 7/8	413 x 251	5	127	20	508	12 1/2	318	41	19
16	19 3/8 x 9 7/8	492 x 251	5	127	24	610	12 1/2	318	48	22

Unit Sizes 12, 14, & 16 Have Flat Oval Inlet Ducts



Standard Construction		
<ul style="list-style-type: none"> <li>1/2" Dual Density, Coated Fiberglass</li> <li>All Insulations Meet NFPA 90A And UL 181</li> <li>All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration</li> </ul>	<ul style="list-style-type: none"> <li>Units Are Constructed With 22 Gauge Casing &amp; Inlet Duct</li> <li>18 Gauge Equivalent Damper Assembly With Integral Blade Seal</li> <li>Control Panel With Dust Cover</li> </ul>	<ul style="list-style-type: none"> <li>Slip &amp; Drive Discharge Connection</li> <li>Inlet Airflow Sensor</li> </ul>