

SANSOME GRILLE - RECOMMENDED SPECIFICATION

Airolite Sansome Grilles are designed and produced to your custom specification to function as architectural accent elements or entire facades that yield sight and solar screening or serve as security barriers. Sansome Grilles are produced from aluminum plate in single or multiple components from 0.250" (6.35 mm) to 0.500" (12.70 mm) thick that enable precise reproduction of intricate or complex geometric patterns. If desired, multiple plate thicknesses may be joined by welding to yield reveals. Where required, optional perimeter channel or tube frames lend rigidity to the assembly and may facilitate installation. Sansome Grilles may be supplied in virtually any geometric pattern that can be detailed in AutoCAD and enable optimum flexibility in design. All materials are available in Airolite's broad array of baked enamel, fluoropolymer and clear or color anodize coatings for durability and compatibility with adjacent components. Please contact your local Airolite representative or the factory for assistance with the layout and design of support systems when required.

GENERAL

Where indicated on plan drawings or described in schedules, furnish and install Sansome Grilles as designed and manufactured by The Airolite Company LLC, Schofield, Wisconsin. Louver screens shall be furnished in the configuration represented on the plan drawings and shall include installation hardware and finishes as specified and required for a complete installation.

SUBMITTALS

Manufacturer shall submit shop drawings incorporating key plans, elevations, sections and details showing profiles, angles and spacing of louver screen blades and frames; unit dimensions related to wall openings and construction; and, anchorage details and locations. Submit theoretical calculations prepared by a professional engineer specializing in the application of welding technology demonstrating that each fillet weld joining blade and frame members will withstand a minimum of 526 pounds of force in shear. Provide samples of manufacturer's finish and color charts showing the full range of colors available.

PRODUCTS

Architectural grilles shall be Airolite Sansome Grilles as follows:

- o Material: Aluminum Plate, Alloy 5052-H32
- o Material Thickness: Specify 0.250" (6.35 mm) to 0.500" (12.70 mm), or as indicated.
- o Grille Depth: Specify 0.250" (6.35 mm) to 6" (152.4 mm), or as indicated.
- o Perimeter Frame: Specify No Frame, Aluminum Channel or Tube, or as indicated.
- o Number of Reveals: Specify number of material thicknesses required or as indicated.
- o Geometric Pattern: As indicated on Contract Drawings.

WELDED ASSEMBLY

Join stationary blade, head and jamb frames with fillet welds concealed from view, unless the size of the louver makes bolted connections between louver sections necessary. Louver blades shall be joined to each jamb frame with a minimum of two fillet welds produced with the Pulsed Gas Metal Arc Welding (GMAW/Mig) process. Each weld shall be a minimum of 1-inch (25.4 mm) in length with a minimum 1/8-inch (3.175 mm) leg. Frames shall be joined at each corner with a full-length GMAW fillet weld with a minimum 1/8-inch (3.175 mm) leg.

STRUCTURAL DESIGN CRITERIA

Manufacturer shall design and furnish all supports required to withstand a wind force of not less than 25 pounds per square foot. Grilles larger than 72-inches wide (1,828.8 mm) x 120-inches high (3,048 mm) or 120-inches (3,048 mm) wide x 72-inches (1,828.8 mm) high will be fabricated and installed in multiple sections. Grille members, frames, mullions and anchorages will be demonstrated to withstand the specified wind design load.