

## **K8206A - RECOMMENDED SPECIFICATION**

### **GENERAL**

Furnish and install where indicated on plans or described in schedules combination drainable stationary and airfoil adjustable blade Louver Type K8206A as designed and manufactured by The AiroLite Company LLC, Schofield, Wisconsin. Louvers shall be furnished with bird screen, insect screen, electric or pneumatic actuators, supports and finishes as specified and as required for a complete installation.

### **SUBMITTALS**

Manufacturer shall submit shop drawings incorporating key plans, elevations, sections and details showing profiles, angles and spacing of louver blades and frames; unit dimensions related to wall openings and construction; and, anchorage details and locations. Provide samples of manufacturer's finish and color charts showing the full range of colors available. For each type of product specified, submit free area, air performance, and water penetration ratings determined in accordance with AMCA Standard 500-L 99 and licensed under the AMCA Certified Ratings Program.

### **PRODUCTS**

Louvers shall be combination type incorporating both drainable stationary and adjustable blades in a single frame. Louvers shall be 6-inches (152 mm) deep and assembled entirely from extruded aluminum. Stationary blades shall be 0.081-inch (2 mm) thick extruded aluminum, alloy 6063-T5. Airfoil adjustable blades shall be 0.063-inch (1.6 mm) thick extruded aluminum, alloy 6063-T5. Frames shall be 0.125-inch (3 mm) thick extruded aluminum, alloy 6063-T5. The stationary blades, louver head and jamb frames shall incorporate integral gutters to minimize water penetration. Stationary blades shall be positioned at 45-degrees and spaced 4.75-inches (120.65 mm) on center. Airfoil adjustable blades shall be fitted with dual-durometer vinyl blade-edge gaskets and compressible stainless steel jamb seals at each jamb frame to restrict air leakage and water penetration when the adjustable blade is closed. The blade linkage assembly shall be fully-enclosed within the louver jamb frame and isolated from the active airstream.

### **STRUCTURAL DESIGN CRITERIA**

Louvers and supports shall be designed and furnished by the manufacturer to withstand a wind force of not less than 25 pounds per square foot. Louvers larger than 60-inches (152 cm) wide x 96-inches (244 cm) high will be fabricated and installed in multiple sections. Louver blades, frames, mullions and anchorages shall be demonstrated to withstand the specified wind design load.

### **PERFORMANCE RATINGS**

|  |   |
|--|---|
| FREE AREA:                               | 7.68 Square Feet (0.71 m <sup>2</sup> ) |
| MINIMUM FREE AREA VELOCITY               |   |
| at Beginning Point of Water Penetration: | 1,221 fpm (6.20 m/s)                    |
| MINIMUM AIR VOLUME FLOW RATE             |   |
| at Beginning Point of Water Penetration: | 9,377 cfm (4.40 m <sup>3</sup> /s)      |
| MAXIMUM STATIC PRESSURE                  |   |
| at Beginning Point of Water Penetration: | 0.14 in. H <sub>2</sub> O (0.035 kPa)   |