

SCH601MDE

Standard Construction

Mounting	Continuous aluminum angle along the jambs
Frame	Heavy gauge extruded 6063-T5 aluminum, 6 in. (152 mm) x 0.081 in. (2 mm) nominal wall thickness
Blades	Horizontal rain resistant design, heavy gauge extruded 6063-T5 aluminum, 0.081 in. (2 mm) nominal wall thickness, positioned on approximately 2 in. (51 mm) centers
Louver Depth	6 in. (152 mm)
Construction	Mechanically fastened
Finish	Mill
Minimum Rough Opening Size	12 in. W x 7 in. H (305 mm W x 178 mm H)
Maximum Rough Opening Size	48.75 in. W x 48.5 in. H (1238 mm W x 1232 mm H)
Wind Load	+/- 150 PSF (7.2 kPa)

Performance Ratings



Airolite certifies that the SCH601MDE louvers shown herein are licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 511 and comply with the requirements of the AMCA Certified Ratings Program. The AMCA Certified Ratings Seal applies to *Water Penetration, Air Performance, and *Wind-Driven Rain ratings. *Ratings include the effect of a sill pan.

Louvers were tested in accordance with AMCA Standard 500-L.



IMPACT RESISTANT LOUVER
Enhanced Protection Level E

See www.AMCA.org for all certified or listed products

This label does not signify AMCA airflow performance certification.

Airolite certifies that the SCH601MDE channel frame and flange/sleeve frame louvers shown herein is approved to bear the AMCA


Listing Label. The ratings shown are based on tests and procedures performed in accordance with AMCA Publications and comply with the requirements of the AMCA Listing Label Program. The AMCA Listing Label applies to Wind Borne Debris Impact Resistant louvers rated for Enhanced Protection with a minimum blade span of less than 12 in. (305 mm) and a maximum unsupported blade span of 46 in. (1168 mm).

Performance of 48 in. x 48 in. (1219 mm x 1219 mm) Louver (channel frame and flange/sleeve frame)

Free Area	
Area	7.58 sq. ft. (0.704 sq. m)
Percent	47.4%
Performance at Beginning Point of Water Penetration	
Free Area Velocity	above 1250 fpm (6.350 m/s)
Max Intake Volume	9475 cfm (4.472 m ³ /s)
Performance at 6,000 CFM (2.832 m³/s) Intake	
Pressure Drop	0.130 in. wg (0.032 kPa)

AMCA 540 Listed Hurricane Louver
Miami-Dade and Florida Product Approved
Extruded Aluminum | Storm Class

Florida Product Approval No.: FL19673
Miami-Dade, FL NOA No.: 20.0929.08 EXP. 12/24/2025




Channel Frame



Options and Accessories

- [Bird Screen](#)
- [Blank Off Panels](#)
- [Filter Rack/Filter](#)
- [Flange/Sleeve Frame](#)
- [Insect Screen](#)
- [Security Bars](#)
- [Variety of Architectural Finishes](#)
- VCD-40 Damper



Flange/sleeve Frame

Product Details

[SCH601MDE Standard Channel Frame Details](#)

[SCH601MDE Optional Flange/Sleeve Frame Details](#)

[Channel and Flange/Sleeve Installation \(#481323 IOM\)](#)

[Miami-Dade County, FL Notice of Acceptance](#)

Structural reinforcing members may be required to adequately support and install multiple louver sections within a large opening. Structural reinforcing members along with any associated installation hardware is not provided by Airolite unless indicated otherwise by Airolite. Options and accessories including, but not limited to, screens, filter racks, louver doors, and blank off panels are not subject to structural analysis unless indicated otherwise by Airolite.



SCH601MDE

AMCA 540 Listed Hurricane Louver
Miami-Dade and Florida Product Approved
Extruded Aluminum | Storm Class

Free Area Chart

Free Area Chart shows free area in square feet and square meters.
(channel frame and flange/sleeve frame)

Louver Height Inches (Meters)	Louver Width in Inches (Meters)						
	12	18	24	30	36	42	48
	0.30	0.46	0.61	0.76	0.91	1.07	1.22
7	0.07	0.12	0.17	0.21	0.26	0.31	0.36
0.18	0.01	0.01	0.02	0.02	0.02	0.03	0.03
12	0.23	0.38	0.53	0.67	0.82	0.97	1.12
0.30	0.02	0.04	0.05	0.06	0.08	0.09	0.10
18	0.47	0.77	1.07	1.36	1.66	1.96	2.26
0.46	0.04	0.07	0.10	0.13	0.15	0.18	0.21
24	0.71	1.16	1.61	2.05	2.50	2.95	3.40
0.61	0.07	0.11	0.15	0.19	0.23	0.27	0.32
30	0.95	1.55	2.15	2.74	3.34	3.94	4.54
0.76	0.09	0.14	0.20	0.25	0.31	0.37	0.42
36	1.11	1.81	2.50	3.20	3.90	4.60	5.30
0.91	0.10	0.17	0.23	0.30	0.36	0.43	0.49
42	1.35	2.19	3.04	3.89	4.74	5.59	6.44
1.07	0.13	0.20	0.28	0.36	0.44	0.52	0.60
48	1.58	2.58	3.58	4.58	5.58	6.58	7.58
1.22	0.15	0.24	0.33	0.43	0.52	0.61	0.70

Core Area Chart

Core Area Chart shows core area in square feet and square meters.
(channel frame and flange/sleeve frame)

Louver Height Inches (Meters)	Louver Width in Inches (Meters)						
	12	18	24	30	36	42	48
	0.30	0.46	0.61	0.76	0.91	1.07	1.22
7	0.20	0.32	0.45	0.57	0.70	0.82	0.95
0.18	0.02	0.03	0.04	0.05	0.07	0.08	0.09
12	0.53	0.86	1.19	1.53	1.86	2.19	2.53
0.30	0.05	0.08	0.11	0.14	0.17	0.20	0.24
18	0.92	1.51	2.09	2.67	3.26	3.84	4.42
0.46	0.09	0.14	0.19	0.25	0.30	0.36	0.41
24	1.32	2.15	2.99	3.82	4.65	5.49	6.32
0.61	0.12	0.20	0.28	0.35	0.43	0.51	0.59
30	1.72	2.80	3.88	4.97	6.05	7.13	8.22
0.76	0.16	0.26	0.36	0.46	0.56	0.66	0.76
36	2.11	3.44	4.78	6.11	7.44	8.78	10.11
0.91	0.20	0.32	0.44	0.57	0.69	0.82	0.94
42	2.51	4.09	5.67	7.26	8.84	10.42	12.01
1.07	0.23	0.38	0.53	0.67	0.82	0.97	1.12
48	2.90	4.74	6.57	8.40	10.24	12.07	13.90
1.22	0.27	0.44	0.61	0.78	0.95	1.12	1.29

Document Links

[Architectural Louvers Catalog](#)

[Finishes & Colors](#)

[Qwik Ship Guide](#)

[Aiolite Warranty Statement](#)



SCH601MDE


AMCA 540 Listed Hurricane Louver
Miami-Dade and Florida Product Approved
Extruded Aluminum | Storm Class

Airflow Resistance

(channel frame and flange/sleeve frame)

Standard Air - 0.075 lb/ft³ (1.2 kg/m³)

Test size 48 in. x 48 in. (1219 mm x 1219 mm)



Model SCH601MDE resistance to airflow (pressure drop) varies depending on louver application (air intake or air exhaust). Free area velocities (shown) are higher than average velocity through the overall louver size. See louver selection information. (Test Figure 5.5-6.5)


Water Penetration

(channel frame and flange/sleeve frame)

Standard Air - 0.075 lb/ft³ (1.2 kg/m³)

Test size 48 in. x 48 in. (1219 mm x 1219 mm)

Test duration of 15 min.



The AMCA Water Penetration Test provides a method for comparing various louver models and designs as to their efficiency in resisting the penetration of rainfall under specific laboratory test conditions. The beginning point of water penetration is defined as that velocity where the water penetration curve projects through 0.01 oz. (3 g) of water (penetration) per sq. ft. (m²) of louver free area. ***The beginning point of water penetration for Model SCH601MDE (channel frame and flange/sleeve frame) is above 1250 fpm (6.350 m/s) free area velocity.** These performance ratings do not guarantee a louver to be weatherproof or stormproof and should be used in combination with other factors including good engineering judgement in selecting louvers.

Wind-Driven Rain Performance

(channel frame and flange/sleeve frame)

3 in./hr. (75 mm/hr.) Rainfall Rate & 29 mph (13 m/s) Wind Velocity				8 in./hr. (203 mm/hr.) Rainfall Rate & 50 mph (22.4 m/s) Wind Velocity			
Ventilation Air Core Velocity fpm (m/s)	Ventilation Air Free Area Velocity fpm (m/s)	Water Penetration Effectiveness %	Water Penetration Classification	Ventilation Air Core Velocity fpm (m/s)	Ventilation Air Free Area Velocity fpm (m/s)	Water Penetration Effectiveness %	Water Penetration Classification
0 (0.0)	0 (0.0)	100	A	0 (0.0)	0 (0.0)		A
98 (0.5)	179 (0.9)	100	A	98 (0.5)	179 (0.9)		A
197 (1.0)	359 (1.8)	100	A	197 (1.0)	359 (1.8)		A
295 (1.5)	538 (2.7)	100	A	295 (1.5)	538 (2.7)		A
394 (2.0)	718 (3.6)	100	A	394 (2.0)	718 (3.6)		A
492 (2.5)	897 (4.6)	100	A	474 (2.4)	864 (4.4)	99.5	A
591 (3.0)	1077 (5.5)	100	A	567 (2.9)	1033 (5.2)	99.6	A
668 (3.4)	1217 (6.2)	100	A	676 (3.4)	1232 (6.3)	99.2	A
763 (3.9)	1391 (7.1)	99.8	A	765 (3.9)	1394 (7.1)	98.5	B
838 (4.3)	1527 (7.8)	98.1	B	860 (4.4)	1567 (8.0)	95.6	B
988 (5.0)	1801 (9.1)	95.4	B	957 (4.9)	1744 (8.9)	88.7	C

Wind-Driven Rain Penetration Classes	
Class	Effectiveness
A	1 to 0.99
B	0.989 to 0.95
C	0.949 to 0.80
D	Below 0.80

Water penetration classification ratings are based on the amount of simulated rain that penetrates the louver during a specific rainfall rate, wind velocity, and intake velocity. Ratings are based on a 39.4 in. x 39.4 in. (1 m x 1 m) core size.

