


# K605

Sightproof Louver | Drainable Louver | Extruded Aluminum

## Standard Construction

<b>Frame</b>	Heavy gauge extruded 6063-T5 aluminum, 5 in. (127 mm) x 0.081 in. (2 mm) nominal wall thickness
<b>Blades</b>	Chevron design, heavy gauge extruded 6063-T5 aluminum, 0.081 in. (2 mm) nominal wall thickness, positioned on approximately 2 in. (51 mm) centers
<b>Louver Depth</b>	5 in. (127 mm)
<b>Construction</b>	Mechanically fastened
<b>Finish</b>	Mill
<b>Minimum Size</b>	12 in. W x 12 in. H (305 mm W x 305 mm H)
<b>Maximum Single Section Size</b>	72 in. W x 144 in. H or 144 in. W x 72 in. H (1829 mm W x 3658 mm H) or (3658 mm W x 1829 mm H)
<b>Wind Load</b>	25 PSF (1.2 kPa)



## Performance Ratings



Airolite certifies that the K605 louvers shown herein are licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 511 and comply with the requirements of the AMCA Certified Ratings Program. The AMCA Certified Ratings Seal applies to Water Penetration and Air Performance ratings.

Louvers were tested in accordance with AMCA Standard 500-L.

### Performance of 48 in. x 48 in. (1219 mm x 1219 mm) Louver

#### Free Area

Area 8.19 sq. ft. (0.761 sq. m)

Percent 51.2%

#### Performance at Beginning Point of Water Penetration

Free Area Velocity 1036 fpm (5.263 m/s)

Max Intake Volume 8485 cfm (4.004 m<sup>3</sup>/s)

#### Performance at 6,000 CFM (2.832 m<sup>3</sup>/s) Intake

Pressure Drop 0.109 in. wg (0.027 kPa)

## Document Links

[Architectural Louvers Catalog](#)

[Finishes & Colors](#)

[Qwik Ship Guide](#)

[Airolite Warranty Statement](#)

## Options and Accessories

- [Bird Screen](#)
- [Blank Off Panels](#)
- [Continuous Blade](#)
- [Extended Sill](#)
- [Filter Rack/Filter](#)
- [Flange Frame](#)
- [Glazing Frame](#)
- [Insect Screen](#)
- [Mounting Angles](#)
- [Security Bars](#)
- [Variety of Architectural Finishes](#)
- Welded Construction

## Standard Details

### [K605 Standard Details](#)

Structural reinforcing members may be required to adequately support and install multiple louver sections within a large opening. Structural reinforcing members along with any associated installation hardware is not provided by Airolite unless indicated otherwise by Airolite. Options and accessories including, but not limited to, screens, filter racks, louver doors, and blank off panels are not subject to structural analysis unless indicated otherwise by Airolite.

 **AIROLITE**<sup>®</sup>  
The look that works.<sup>™</sup>

# K605

Sightproof Louver | Drainable Blade | Extruded Aluminum

## Free Area Chart

Free Area Chart shows free area in square feet and square meters.

Louver Height Inches (Meters)	Louver Width in Inches (Meters)											
	12	24	36	48	60	72	84	96	108	120	132	144
0.30	0.30	0.61	0.91	1.22	1.52	1.83	2.13	2.44	2.74	3.05	3.35	3.66
<b>12</b>	<b>0.26</b>	<b>0.62</b>	<b>0.97</b>	<b>1.32</b>	<b>1.67</b>	<b>1.98</b>	<b>2.33</b>	<b>2.69</b>	<b>3.04</b>	<b>3.39</b>	<b>3.70</b>	<b>4.05</b>
0.30	0.02	0.06	0.09	0.12	0.16	0.18	0.22	0.25	0.28	0.31	0.34	0.38
<b>24</b>	<b>0.72</b>	<b>1.68</b>	<b>2.65</b>	<b>3.61</b>	<b>4.57</b>	<b>5.42</b>	<b>6.38</b>	<b>7.34</b>	<b>8.30</b>	<b>9.27</b>	<b>10.11</b>	<b>11.07</b>
0.61	0.07	0.16	0.25	0.34	0.42	0.50	0.59	0.68	0.77	0.86	0.94	1.03
<b>36</b>	<b>1.18</b>	<b>2.75</b>	<b>4.33</b>	<b>5.90</b>	<b>7.47</b>	<b>8.85</b>	<b>10.42</b>	<b>12.00</b>	<b>13.57</b>	<b>15.14</b>	<b>16.52</b>	<b>18.09</b>
0.91	0.11	0.26	0.40	0.55	0.69	0.82	0.97	1.11	1.26	1.41	1.53	1.68
<b>48</b>	<b>1.64</b>	<b>3.82</b>	<b>6.01</b>	<b>8.19</b>	<b>10.37</b>	<b>12.29</b>	<b>14.47</b>	<b>16.65</b>	<b>18.84</b>	<b>21.02</b>	<b>22.93</b>	<b>25.12</b>
1.22	0.15	0.35	0.56	0.76	0.96	1.14	1.34	1.55	1.75	1.95	2.13	2.33
<b>60</b>	<b>2.10</b>	<b>4.89</b>	<b>7.69</b>	<b>10.48</b>	<b>13.27</b>	<b>15.72</b>	<b>18.51</b>	<b>21.31</b>	<b>24.10</b>	<b>26.90</b>	<b>29.34</b>	<b>32.14</b>
1.52	0.20	0.45	0.71	0.97	1.23	1.46	1.72	1.98	2.24	2.50	2.73	2.99
<b>72</b>	<b>2.55</b>	<b>5.96</b>	<b>9.36</b>	<b>12.77</b>	<b>16.17</b>	<b>19.15</b>	<b>22.56</b>	<b>25.97</b>	<b>29.37</b>	<b>32.78</b>	<b>35.76</b>	<b>39.16</b>
1.83	0.24	0.55	0.87	1.19	1.50	1.78	2.10	2.41	2.73	3.05	3.32	3.64
<b>84</b>	<b>3.01</b>	<b>7.03</b>	<b>11.04</b>	<b>15.06</b>	<b>19.08</b>	<b>22.59</b>						
2.13	0.28	0.65	1.03	1.40	1.77	2.10						
<b>96</b>	<b>3.47</b>	<b>8.10</b>	<b>12.72</b>	<b>17.35</b>	<b>21.98</b>	<b>26.02</b>						
2.44	0.32	0.75	1.18	1.61	2.04	2.42						
<b>108</b>	<b>3.93</b>	<b>9.16</b>	<b>14.40</b>	<b>19.64</b>	<b>24.88</b>	<b>29.46</b>						
2.74	0.37	0.85	1.34	1.82	2.31	2.74						
<b>120</b>	<b>4.39</b>	<b>10.23</b>	<b>16.08</b>	<b>21.93</b>	<b>27.78</b>	<b>32.89</b>						
3.05	0.41	0.95	1.49	2.04	2.58	3.06						
<b>132</b>	<b>4.84</b>	<b>11.30</b>	<b>17.76</b>	<b>24.22</b>	<b>30.68</b>	<b>36.33</b>						
3.35	0.45	1.05	1.65	2.25	2.85	3.38						
<b>144</b>	<b>5.30</b>	<b>12.37</b>	<b>19.44</b>	<b>26.51</b>	<b>33.58</b>	<b>39.76</b>						
3.66	0.49	1.15	1.81	2.46	3.12	3.69						




# K605

Sightproof Louver | Drainable Blade | Extruded Aluminum

## Airflow Resistance

Standard Air - 0.075 lb/ft<sup>3</sup> (1.2 kg/m)

Test size 48 in. x 48 in. (1219 mm x 1219 mm)




Model K605 resistance to airflow (pressure drop) varies depending on louver application (air intake or air exhaust). Free area velocities (shown) are higher than average velocity through the overall louver size. See louver selection information. (Test Figure 5.5-6.5)

## Water Penetration

Standard Air - 0.075 lb/ft<sup>3</sup> (1.2 kg/m)

Test size 48 in. x 48 in. (1219 mm x 1219 mm)

Test duration of 15 min.



The AMCA Water Penetration Test provides a method for comparing various louver models and designs as to their efficiency in resisting the penetration of rainfall under specific laboratory test conditions. The beginning point of water penetration is defined as that velocity where the water penetration curve projects through 0.01 oz. (3 g) of water (penetration) per sq. ft. (m<sup>2</sup>) of louver free area. **\*The beginning point of water penetration for Model K605 is 1036 fpm (5.263 m/s) free area velocity.** These performance ratings do not guarantee a louver to be weatherproof or stormproof and should be used in combination with other factors including good engineering judgement in selecting louvers.

