

**T9612/9612/CB9612/FCB9612 - RECOMMENDED SPECIFICATION**

**GENERAL**

Furnish and install where indicated on plans or described in schedules Acoustic Louver Type T9612 designed and manufactured by The AiroLite Company LLC, Schofield, Wisconsin. Louvers shall be furnished with bird screen, insect screen, supports, installation hardware and finishes as specified and as required for a complete installation. If aluminum construction is preferred, specify Louver Type T9612 with visible vertical mullions or Louver Type CB9612 with concealed vertical mullions. If galvanized steel construction is preferred, specify Louver Type 9612 with visible mullions or Louver Type FCB9612 with concealed vertical mullions.

**SUBMITTALS**

Manufacturer shall submit shop drawings incorporating key plans, elevations, sections and details showing profiles, angles and spacing of louver blades and frames; unit dimensions related to wall openings and construction; and, anchorage details and locations. Provide samples of manufacturer's finish and color charts showing the full range of colors available. For each type of product specified, submit free area and air performance ratings shall be determined in accordance with AMCA Standard 500-L 99 and Licensed the AMCA Certified Ratings Program.

**PRODUCTS**

Louvers shall be acoustic type incorporating stationary, sightproof blades in a single frame. Louvers shall be 12-inches (304.8 mm) deep and assembled entirely from fabricated aluminum components (or select material type from the table above). Blades and frames shall be 0.080-inch (2 mm) thick aluminum, alloy 5052-H32 (or select material thickness and material from the table above). Blades shall be positioned at 45-degrees and spaced 5-inches (127 mm) on center. Each blade and top and bottom frame cavity shall be filled with fiberglass acoustic insulation to absorb the transmission of sound. Acoustic insulation shall be held in place by 0.032-inch (0.81 mm) thick perforated aluminum panels.

**STRUCTURAL DESIGN CRITERIA**

Manufacturer shall design and furnish all supports required to withstand a wind force of not less than 25 pounds per square foot. Louvers larger than 60-inches (152 cm) wide x 120-inches (305 cm) high will be fabricated and installed in multiple sections. Louver blades, frames, mullions and anchorages shall be demonstrated to withstand the specified wind design load.

**PERFORMANCE RATINGS**

FREE AREA:	4.27 Square Feet (0.40 m <sup>2</sup> )
MINIMUM FREE AREA VELOCITY	
at Beginning Point of Water Penetration:	830 fpm (4.22 m/s)
MINIMUM AIR VOLUME FLOW RATE	
at Beginning Point of Water Penetration:	3,544 cfm (1.67 m <sup>3</sup> /s)
MAXIMUM STATIC PRESSURE	
at Beginning Point of Water Penetration:	0.12 in. H <sub>2</sub> O (0.030 kPa)