



— Factory Piping
 - - - Field Piping By Others

Controller/Actuator-CSP-4702, 24 VAC, 4 VA
 Thermostat-CTE-5202
 Reheat Module-REE-5002, 24 VAC

Notes:

- 1) Maximum connected 24 Vac load connections not to exceed 20 VA total, 24 VAC NEC Class 2 for field connected loads.

Wiring Notes: In case of HW Coil, HW Valve and associated Stage 1 wiring is field installed by others.

Transformer Options:
 861N, - No Xformer
 861A, - 120 / 24
 861C, - 277 / 24
 861F, - 240 / 24
 861E, - Primary Voltage to match electric heat / 24

FVCD 861

(CDS) ATU\CONTROL DIAGRAMS\ANALOG\

Control Wiring Diagram

COOLING ONLY WITH FAN RELAY
 HW VALVE OPTION (FIELD INSTALLED)

Phone: 715.359.6171
 Fax: 715.355.2399
 Parts : 800.355.5354
 gfcinfo@greenheck.com
 www.greenheck.com

N/A	B	Removed logo	7/14/21	CG
NA	A	UPDATED TO NEW FORMAT	06/16/17	RML
ECN. No.	Rev	Description	Date	Rev'd By:

Unless Otherwise Specified:
 1. Dimensions Are In Inches.
 2. Tolerances Are:
 Fractions Decimals Angles
 $\pm .X = .1$
 $\pm .XX = .02$
 $\pm .XXX = .010$
 $\pm 1/32$ $\pm 1^\circ$

DWN. BY	DG	DATE	10/13/06	DWG. NO.		REV.	
CHK'D BY	DG	SCALE	NTS	FVCD861		B	