



— Factory Piping  
--- Field Piping By Others

**Notes:**

- Maximum connected 24 Vac load connections not to exceed 20 VA total, 24 VAC NEC Class 2 for field connected loads.

Controller/Actuator-CSP-4702, 24 VAC, 4 VA  
Thermostat-CTE-5202  
Reheat Module-REE-5002, 24 VAC

**FVCD 861**

(CDS) ATU\CONTROL DIAGRAMS\ANALOG\

# Control Wiring Diagram

**COOLING ONLY WITH FAN RELAY  
HW VALVE OPTION (FIELD INSTALLED)**

N/A	B	Removed logo	7/14/21	CG
NA	A	UPDATED TO NEW FORMAT	06/16/17	RML
ECN. No.	Rev	Description	Date	Rev'd By:

Unless Otherwise Specified:		
1. Dimensions Are In Inches.		
2. Tolerances Are:		
Fractions	Decimals	Angles
±.X = .1	±.XX = .02	±1°
±1/32	±.XXX = .010	

DWN. BY	DG	DATE	10/13/06	DWG. NO.	FVCD861	REV.	B
CHK'D BY	DG	SCALE	NTS				