



——— Factory Piping
 - - - Field Piping By Others

Controller/Actuator-CSP-4702, 24 VAC, 4 VA
 Thermostat-CTE-5202
 Reheat Module-REE-5002, 24 VAC

Notes:

1) Maximum connected 24 Vac load connections not to exceed 20 VA

Transformer Options:
861E, - Primary Voltage to match electric heat / 24

FVCD 861-SCR
(CDS) ATU\CONTROL DIAGRAMS\ANALOG\

Control Wiring Diagram

FAN POWERED AIR TERMINAL UNIT
COOLING WITH SCR ELECTRIC HEAT

Phone: 715.359.6171
Fax: 715.355.2399
Parts : 800.355.5354
gfcinfo@greenheck.com
www.greenheck.com

| | | | | |
|----------|-----|---------------------------|----------|-----------|
| N/A | D | Removed logo | 7/14/21 | CG |
| N/A | C | UPDATED TO NEW FORMAT | 06/19/17 | RML |
| N/A | B | Changed to REE-5001 Relay | 1/29/16 | DSG |
| N/A | A | Changed to CTE-5104 Stat. | 4/07/15 | DSG |
| ECN. No. | Rev | Description | Date | Rev'd By: |

| | | | | |
|------------------------------|--------------|--------|----------|--------------|
| Unless Otherwise Specified: | | | | |
| 1. Dimensions Are In Inches. | | | | |
| 2. Tolerances Are: | | | | |
| Fractions | Decimals | Angles | | |
| ±1/32 | ±.X = .1 | ±1° | | |
| | ±.XX = .02 | | | |
| | ±.XXX = .010 | | | |
| DWN. BY | DSG | DATE | 03/26/13 | DWG. NO. |
| CHK'D BY | | SCALE | NTS | FVCD861E-SCR |
| | | | | REV. D |