

# DM-3 | HVLS

5-FOOT FAN DIAMETER

## Elevated Engineering

Create an ideal space in your facility with the stylish Greenheck DM-3. The perfect balance of power and elegance, the DM-3 boosts occupant comfort and enhances the interior design of any commercial or institutional building. Plus, its advanced direct drive motor and curved airfoil design deliver quiet and efficient performance you can feel, with cost savings you can see.

### DIAMETER

- 5-foot fan diameter

### AIRFLOW AND COOLING

- Airflow range up to 7,113 cfm
- Cooling effect up to 7°F

### MOTOR AND VOLTAGE

- 1/10 hp, direct drive motor
- Reversible operation
  - 115V/1-phase

### MOUNTING OPTIONS

- Universal mounting to any ceiling structure

### WARRANTY


- 1-year mechanical
- 1-year electrical

## PRIMARY APPLICATIONS

Office Spaces | Education Facilities | Retail Stores | Restaurants and Bars  
Fitness Centers | Hotels | Multifamily Housing

# DM-3 | HVLS

5-FOOT FAN DIAMETER



## STANDARD FEATURES

### ELEVATED DESIGN



Fans feature a sleek, modern design that delivers comfortable air movement with style.

### UNIVERSAL CEILING MOUNT



Designed to mount to any ceiling structure using field-supplied hardware. Universal mount also includes a pivoting knuckle joint to accommodate any ceiling pitch.

### DIRECT DRIVE MOTOR AND DRIVER



Lightweight, direct drive motor is up to 20% more efficient and 10 dBA quieter than traditional motors. Factory-programmed motor driver reduces installation time by eliminating complicated programming in the field.

### AIRFOILS



Curved polymer airfoils are designed to maximize airflow, boost efficiency, and optimize coverage area. Bone White or Flat Black finish options provide a clean and classic look in any space.

### ADVANCED SAFETY FEATURES



Factory-installed, redundant mechanical safety systems ensure proper function and peace of mind. Smart electronic safety features include:

- Impact detection for immediate fan shutdown
- Over-current and over-speed protection

### WIRELESS RF CONTROLLER



Handheld, wireless RF controller allows for flexible operation of connected fans. Controller features include:

- Factory-paired with motor driver
- Six speed settings and direction control
- Wall mount

## PERFORMANCE DATA

FAN SIZE (ft)	MAX AIRFLOW (CFM)	MAX COVERAGE AREA (ft <sup>2</sup> )	MAX RPM	MOTOR SIZE (HP)	SOUND (dBA)	WEIGHT* (lbs)
5	7,113	900	120	1/10	22	16

\*Weight does not include accessories or optional features.

[greenheck.com/hvls](https://greenheck.com/hvls)

P.O. Box 410 | Schofield, WI 54476 | 715-359-6171 00.F&V.NB025 R2 2-2024 © 2024 Greenheck Fan Corp.

 **GREENHECK**  
Building Value in Air.