

Modular Open Array

AHU RETROFIT SOLUTION



MOA – A Customized Retrofit Solution

Experience a seamless retrofit assembly with Greenheck's packaged Modular Open Array (MOA), designed by you, to fit your custom application. Minimize downtime and reduce labor costs with **plug-and-play wiring connections** for quick and easy installation. The MOA configurable fan array features lightweight, easy-to-assemble components that ship to the jobsite knocked down for field installation.

EFFICIENT INSTALLATION

- Complete packaged assembly includes electrical panels, wiring, modular structure, and fans.
- Lightweight modular components allow for efficient installation in even the tightest spaces.
- Components come clearly labeled with easy-to-follow installation instructions and plug-and-play wiring connections.

PREWIRED CONTROLS PACKAGE

- Single touchscreen control panel operates up to 64 fans with no limit on total number of fans within a system.
- Seamless integration with existing electrical infrastructure and flexible signal with Building Management Systems.

PROVEN PERFORMANCE

- Optimized performance, laboratory tested.
- Efficient Vari-Green® EC motor technology allows endless capacity starting at 1,500 cfm with a static pressure up to 8 in. wg.

APPLICATIONS

Air Handling Unit (AHU) Retrofits | Airports | Built-Up Systems | Clean Rooms | Data Centers
Hospitals | Health Care | Office Buildings | Other Large Buildings | Pharmaceuticals | Universities

greenheck.com

P.O. Box 410 | Schofield, WI 54476 | 715-359-6171 August 2024 © 2024 Greenheck Fan Corp.

 **GREENHECK**
Building Value in Air.