



Model: XG-CC1-1 Cubed Core 1"x1"x1" - Flush Surface Mount
 XG-CC1-6 Cubed Core 1"x1"x1" - T-Bar Lay-In


XG-CC1-1 - Flush Surface Mount




Face View



XG-CC1-6 - T-Bar Lay-In



Face View




1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	XG-OBDA - Steel Opposed Blade Damper XG-OBDA - Aluminum OBD XG-L9 - Equalizing Grid XG-PF - Plaster Frame XG-TBPF - T-Bar Plaster Frame XG-TR - Square to Round Transition XG-TR-Deep - Deep Transition XG-LIPF - Lay-In Plaster Frame	IS - Insect Screen NSH - No Screw Holes CM - Concealed Mount	<ul style="list-style-type: none"> • Odd/Fractional Sizes Available for additional charge • Oversized Units made in multiple sections • Largest single section is 48x48 • Mullion strips provided for joining units in field • Available in MRI-compatible aluminum construction


All Dimensions $\pm 1/16"$

Model: XG-CC1-8 Cubed Core 1"x1"x1" - Tegular Module
 XG-CC1-9 Cubed Core 1"x1"x1" - Bolt Slot / Donn Fineline Module

XG-CC1-8 - Tegular Module




Face View




XG-CC1-9 - Bolt Slot / Donn Fineline Module

Model: XG-CC1-9 - Side wall Return Grille
 Bolt Slot Ceiling Grid



Face View



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	XG-OBDA - Steel Opposed Blade Damper XG-OBDA - Aluminum OBD XG-L9 - Equalizing Grid XG-PF - Plaster Frame XG-TBPF - T-Bar Plaster Frame XG-TR - Square to Round Transition XG-TR-Deep - Deep Transition XG-LIPF - Lay-In Plaster Frame	IS - Insect Screen NSH - No Screw Holes CM - Concealed Mount	<ul style="list-style-type: none"> • Odd/Fractional Sizes Available for additional charge • Oversized Units made in multiple sections • Largest single section is 48x48 • Mullion strips provided for joining units in field • Available in MRI-compatible aluminum construction

All Dimensions $\pm 1/16"$