



— Factory Piping
 - - - Field Piping By Others

Controller/Actuator-CSP-4702, 24 VAC, 4 VA
 Thermostat-CTE-5202
 Reheat Module-REE-5002, 24 VAC

- Notes:
 1) Maximum connected 24 Vac load connections not to exceed 20 VA total, 24 VAC NEC Class 2 for field connected loads.

Transformer Options:
 860N, - No Xformer
 860A, - 120 / 24
 860C, - 277 / 24
 860F, - 240 / 24

FVCD 860

(CDS) ATU\CONTROL DIAGRAMS\ANALOG\

Control Wiring Diagram

COOLING ONLY WITH FAN RELAY

Phone: 715.359.6171
 Fax: 715.355.2399
 Parts : 800.355.5354
 gfcinfo@greenheck.com
 www.greenheck.com

N/A	H	Removed logo	7/12/21	CG
N/A	G	UPDATED TO NEW FORMAT	06/16/17	RML
N/A	F	REMOVED 861 REFERENCES	10/13/06	DSG
ECN. No.	Rev	Description	Date	Rev'd By:

Unless Otherwise Specified:
 1. Dimensions Are In Inches.
 2. Tolerances Are:
 Fractions Decimals Angles
 $\pm .X = .1$
 $\pm 1/32 \quad \pm .XX = .02 \quad \pm 1^\circ$
 $\pm .XXX = .010$

DWN. BY	DG	DATE	10/14/02	DWG. NO.	FVCD860	REV.	H
CHK'D BY	DG	SCALE	NTS				