



——— Factory Piping
 - - - Field Piping By Others

Controller/Actuator-CSP-4702, 24 VAC, 4 VA
 Thermostat-CTE-5202
 Reheat Module-REE-5002, 24 VAC

- Notes:
- Maximum connected 24 Vac load connections not to exceed 20 VA total, 24 VAC NEC Class 2 for field connected loads.

Transformer Options:

- 860N, - No Xformer
- 860A, - 120 / 24
- 860C, - 277 / 24
- 860F, - 240 / 24

FVCD 860

(CDS) ATU\CONTROL DIAGRAMS\ANALOG\

Control Wiring Diagram

COOLING ONLY WITH FAN RELAY

Phone: 715.359.6171
 Fax: 715.355.2399
 Parts : 800.355.5354
 gfcinfo@greenheck.com
 www.greenheck.com

ECN. No.	Rev	Description	Date	Rev'd By:
N/A	H	Removed logo	7/12/21	CG
N/A	G	UPDATED TO NEW FORMAT	06/16/17	RML
N/A	F	REMOVED 861 REFERENCES	10/13/06	DSG

Unless Otherwise Specified: 1. Dimensions Are In Inches. 2. Tolerances Are: Fractions Decimals Angles $\pm 1/32$ $\pm .X = .1$ $\pm 1^\circ$ $\pm .XX = .02$ $\pm .XXX = .010$		DWN. BY DG DATE 10/14/02 CHK'D BY DG SCALE NTS		DWG. NO. FVCD860		REV. H	
--	--	---	--	------------------	--	--------	--