

C800H

Architectural Canopy | Extruded Aluminum

Standard Construction

Hood Material	Aluminum 5052-H35
Hood Material Thickness	0.100 in. (2.54 mm)
Canopy Height	8 in. (203.2 mm)
Frame Material	Extruded aluminum 6063-T5
Frame Material Thickness	0.125 in. (3.18 mm)
Standard Fascia	8 in. (203.2 mm) flat plate
Optional Fascia	Channel: 8 in. (203.2 mm), 10 in. (254 mm), and 12 in. (304.8 mm) or Flat: 12 in. (304.8 mm) - Field installed
Mounting	Direct
Construction	Mechanically Fastened
Tieback Material	Extruded aluminum square or round adjustable tube



Canopies frame members are heavy gauge extruded 6063-T5 aluminum, 8 in. (203 mm) channel with integrated gutter and snap cover feature. Soffit hood is heavy gauge extruded 6063-T5 aluminum, 8 in. (203 mm) channel panels. Internal supports are heavy gauge extruded 6063-T5 aluminum, 4 in. (101 mm) I-beam.

Standard Details

[C800H Standard Details](#)

Document Links

[Canopy C800H](#)

[Aiolite Warranty Statement](#)

AIROLITE[®]
The look that works.[™]