

# C800SH

Architectural Canopy | Extruded Aluminum

## Standard Construction

<b>Hood Material</b>	Aluminum 6005-T5
<b>Hood Material Thickness</b>	0.100 in. (2.54 mm)
<b>Canopy Height</b>	8 in. (203.2 mm)
<b>Frame Material</b>	Extruded aluminum 6063-T5
<b>Frame Material Thickness</b>	0.250 in. (6.35 mm)
<b>I-Beam Material Thickness</b>	0.250 in. (6.35 mm)
<b>Standard Fascia</b>	8 in. (203.2 mm) flat plate
<b>Optional Fascia</b>	Channel, 8 in. (203.2 mm), 10 in. (254 mm), and 12 in. (304.8 mm) - Field installed
<b>Mounting</b>	Extruded aluminum wall bracket
<b>Construction</b>	Mechanically Fastened
<b>Tieback Material</b>	Extruded aluminum square or round adjustable tube



Canopies frame members are heavy gauge extruded 6063-T5 aluminum, 8 in. (203 mm) channel with integrated gutter. Soffit hood is heavy gauge extruded 6005-T5 aluminum, 8 in. (203 mm) channel panels. Internal supports are heavy gauge extruded 6063-T5 aluminum, 4 in. (101 mm) I-beam.

## Standard Details

[C800SH Standard Details](#)

## Document Links

[Canopy C800SH](#)

[Aiolite Warranty Statement](#)

**AIROLITE**<sup>®</sup>  
The look that works.<sup>™</sup>