




LOW VOLTAGE – C.C.W.




HIGH VOLTAGE – C.C.W.



DUAL VOLTAGE CAPACITOR START
NO OVERLOAD SELECT ROTATION.

LOW VOLTAGE C.C.W. ROTATION
SHOWN. TO REVERSE, INTERCHANGE
RED WITH BLACK LEAD ON
TERMS 1 AND 5.

FOR HIGH VOLTAGE C.C.W. ROT.
FIRST REMOVE BROWN JUMPER
FROM TERM. 4 AND ATTACH TO
TERM 3. CONNECT YELLOW
LEAD TO TERM. 4 AND ORANGE
LEAD TO TERM. 3. TO REVERSE
INTERCHANGE RED WITH BLACK
LEADS ON TERMS 1 AND 5.

				TOLERANCES UNLESS SPECIFIED			DRAWN PGK 06-20-1996			
				DEC.	INCHES		CHK MRB 07-10-1996			
				.X	± -		APPD GK 07-10-1996			
				.XX	± -		SCALE 5=8			
				.XXX	± -		REF			
7	M1 & M2 WERE REVERSED IN MAIN VIEW	CN 31843	DRS 09-28-2002	ML	.XXX	± -	TITLE CONNECTION DIAGRAM			
6	REDRAWN ON CADD, NO CHANGES		PGK 07-10-1996		.XXXX	± -	MAT'L.			
NO.	REVISION	BY & DATE	CHK	ANG	± -	FINISH	PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE 102005-1		SIZE	DRAWING NO.	PAGE	OF
				DIST	WP		A	102005-1	7	7