







Product Features:








- Perforated diffusers provide a smooth continuous ceiling aesthetic
- Available in Extruded Aluminum construction
- Face panel uses 51% free area perforated metal
- Return style diffusers do not include pattern deflectors
- Optimal performance with low pressure drop and sound levels


Finishes

01 - White ¹	03 - Black	¹ White Finish is suitable for a primer coat if field painting is required.
		
02 - Satin Silver	24 - Mill	
		
28 - Custom Color	22 - BBP	Black Back Pan White Face
		


Product Pressure Drop Performance

Optional Accessories:


	Opposed Blade Damper D7 - Steel D7A - Aluminum
	TBPF - T-Bar Plaster Frame LIPF - Lay-In Plaster Frame
	RSD - Radial Shutter Damper
	BDS - Butterfly Damper
	TR - Square to Round Transition TR-Deep - TR-Deep Transition
	L9 - Equalizing Damper
	G3 - Equalizing Damper



Listed Nominal	Largest Size
Face	Neck
12 x 12	6 x 6
14 x 14	8 x 8
15 x 15	9 x 9
16 x 16	10 x 10
18 x 18	12 x 12
20 x 20	14 x 14
21 x 21	15 x 15
24 x 12	18 x 6
24 x 24	16 x 16
48 x 24	18 x 18




Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.



Low Profile - Side View


Listed Nominal	Largest Size
Face	Neck
12 x 12	10 x 10
14 x 14	12 x 12
15 x 15	13 x 13
16 x 16	14 x 14
18 x 18	16 x 16
20 x 20	18 x 18
21 x 21	19 x 19
24 x 12	22 x 10
24 x 24	22 x 22
48 x 24	46 x 22

Low Profile backpan is used on full-faced units only.
Used when neck size and overall size has 2 inch difference.
Example: 10x10 neck on 12x12 module




Face View

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.




Listed Nominal	Largest Size
Face	Neck
12 x 12	6 x 6
20 x 20	14 x 14
24 x 12	18 x 6
-	-
36 x 12	18 x 6
36 x 24	16 x 16
48 x 12	18 x 6
48 x 24	18 x 18



Face View


Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.

Concealed Spring
Latches & Hinges




Side View

Listed Nominal	Largest Size
Face	Neck
24 x 24	18 x 18




Face View

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.




Listed Nominal	Largest Size
Face	Neck
24 x 24	14 x 14




Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.

Neck Size = Listed Size - $\frac{1}{8}$



Side View

Listed Nominal	Largest Size
Face	Neck
24 x 24	18 x 18



Face View

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.