



Product Features:

- Available for straight and curved applications
- Model LAD is available in slot widths from 1" to 3" wide
- Available with 1 or 2 slots
- Longest single section is 96"
- Various frame types are available for different applications:
 - AA Frame – Exposed Flange
 - CC Frame – Concealed Tape and Spackle
 - FF Frame – Flush Channel Frame
 - FH Frame – Offset Flush Frame
 - GG Frame – Beveled Frame
- Can come with hanger brackets for concealed mounting
- Available with standard for combo blade pattern controllers for horizontal or vertical applications
- Combination frames are available when two different frames are required on a single linear

Finishes

20 - White/Black



03 - Black



02 - Satin Silver



24 - Mill




28 - Custom Color




¹ White Finish is suitable for a primer coat if field painting is required.

Optional Accessories:




Standard Blades




Combo Blades


CFD Throw Pattern Visualization

Horizontal Throw





Vertical Throw












Open End (O)	End Cap		End Border		Mitered Border	
X = 0	1 EC:	X = 0	1 EB:	$X = \frac{3}{4}$	MO:	$X = \frac{3}{4}$
	2 EC:	X = 0	2 EB:	$X = 1\frac{1}{2}$	MM:	$X = 1\frac{1}{2}$







		Face Width		Neck Width					Concealed Mount	
Model	S	A	A	W1	W1	B	CB	H	W2	W2
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot	Border Width	Border Width	Height	1 Slot	2 Slot
LAD-AA-10	1	4 1/4	7 3/16	3 1/4	6 3/16	1 5/8	1 15/16	2	4	7
LAD-AA-15	1 1/2	4 3/4	8 3/16	3 3/4	7 3/16	1 5/8	1 15/16	2	4 1/2	8
LAD-AA-20	2	5 1/4	9 3/16	4 1/4	8 3/16	1 5/8	1 15/16	2	5	9
LAD-AA-25	2 1/2	6 3/4	12 3/16	5 3/4	11 3/16	2 1/8	2 15/16	2 1/2	6 1/2	12
LAD-AA-30	3	7 1/4	13 3/16	6 1/4	12 3/16	2 1/8	2 15/16	2 1/2	7	13









						
Open End (O)	End Cap		End Border		Mitered Border	
X = 0	1 EC:	X = 0	1 EB:	X = $\frac{3}{4}$	MO:	X = $\frac{3}{4}$
	2 EC:	X = 0	2 EB:	X = $1\frac{1}{2}$	MM:	X = $1\frac{1}{2}$


LAD-AC CM




		Face Width		Neck Width					Concealed Mount	
Model	S	A	A	W1	W1	B	CB	H	W2	W2
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot	Border Width	Border Width	Height	1 Slot	2 Slot
LAD-AC-10	1	4 1/4	7 3/16	3 1/4	6 3/16	1 5/8	1 15/16	2	4	7
LAD-AC-15	1 1/2	4 3/4	8 3/16	3 3/4	7 3/16	1 5/8	1 15/16	2	4 1/2	8
LAD-AC-20	2	5 1/4	9 3/16	4 1/4	8 3/16	1 5/8	1 15/16	2	5	9
LAD-AC-25	2 1/2	6 3/4	12 3/16	5 3/4	11 3/16	2 1/8	2 15/16	2 1/2	6 1/2	12
LAD-AC-30	3	7 1/4	13 3/16	6 1/4	12 3/16	2 1/8	2 15/16	2 1/2	7	13


Standard Blade

Combo Blades


			
Open End (O)	End Cap	End Border	Mitered Border
X = 0	1 EC: X = 0	1 EB: X = $\frac{3}{4}$	MO: X = $\frac{3}{4}$
	2 EC: X = 0	2 EB: X = $1\frac{1}{2}$	MM: X = $1\frac{1}{2}$


LAD-CC CM



		Face Width		Neck Width					Concealed Mount	
Model	S	A	A	W1	W1	B	CB	H	W2	W2
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot	Border Width	Border Width	Height	1 Slot	2 Slot
LAD-CC-10	1	4 1/4	7 3/16	3 1/4	6 3/16	1 5/8	1 15/16	2	4	7
LAD-CC-15	1 1/2	4 3/4	8 3/16	3 3/4	7 3/16	1 5/8	1 15/16	2	4 1/2	8
LAD-CC-20	2	5 1/4	9 3/16	4 1/4	8 3/16	1 5/8	1 15/16	2	5	9
LAD-CC-25	2 1/2	6 3/4	12 3/16	5 3/4	11 3/16	2 1/8	2 15/16	2 1/2	6 1/2	12
LAD-CC-30	3	7 1/4	13 3/16	6 1/4	12 3/16	2 1/8	2 15/16	2 1/2	7	13





Standard Blade




Combo Blade



	
Open End (O)	End Cap
X = 0	1 EC: X = 0
	2 EC: X = 0





LAD-FF CM


Model	S Slot Width	Face Width		Neck Width		B Border Width	CB Border Width	H Height	Concealed Mount	
		A 1 Slot	A 2 Slot	W1 1 Slot	W1 2 Slot				W2 1 Slot	W2 2 Slot
LAD-FF-10	1	3 1/4	6 3/16	3 1/4	6 3/16	1 1/8	1 15/16	1 15/16	4	7
LAD-FF-15	1 1/2	3 3/4	7 3/16	3 3/4	7 3/16	1 1/8	1 15/16	1 15/16	4 1/2	8
LAD-FF-20	2	4 1/4	8 3/16	4 1/4	8 3/16	1 1/8	1 15/16	1 15/16	5	9
LAD-FF-25	2 1/2	5 3/4	11 3/16	5 3/4	11 3/16	1 5/8	2 15/16	2 9/16	6 1/2	12
LAD-FF-30	3	6 1/4	12 3/16	6 1/4	12 3/16	1 5/8	2 15/16	2 9/16	7	13







	
Open End (O)	End Cap
X = 0	1 EC: X = 0
	2 EC: X = 0






		Face Width		Neck Width						Concealed Mount	
Model	S	A	A	W1	W1	B	C	CB	H	W2	W2
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot	F Face	A Face	Border Width	Height	1 Slot	2 Slot
LAD-FA-10	1	3 3/4	6 3/16	3 1/4	5 11/16	1 1/8	1 5/8	1 15/16	1 15/16	4	7
LAD-FA-15	1 1/2	4 1/4	7 3/16	3 3/4	6 11/16	1 1/8	1 5/8	1 15/16	1 15/16	4 1/2	8
LAD-FA-20	2	4 3/4	8 3/16	4 1/4	7 11/16	1 1/8	1 5/8	1 15/16	1 15/16	5	9
LAD-FA-25	2 1/2	6 1/4	11 3/16	5 3/4	11 11/16	1 5/8	2 1/8	2 15/16	2 9/16	6 1/2	12
LAD-FA-30	3	6 3/4	12 3/16	6 1/4	12 11/16	1 5/8	2 1/8	2 15/16	2 9/16	7	13







	
Open End (O)	End Cap
X = 0	1 EC: X = 0
	2 EC: X = 0






		Face Width		Neck Width						Concealed Mount	
Model	S	A	A	W1	W1	B	C	CB	H	W2	W2
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot	F Face	C Face	Border Width	Height	1 Slot	2 Slot
LAD-FC-10	1	3 3/4	6 3/16	3 1/4	6 3/16	1 1/8	1 5/8	1 15/16	1 15/16	4	7
LAD-FC-15	1 1/2	4 1/4	7 3/16	3 3/4	7 3/16	1 1/8	1 5/8	1 15/16	1 15/16	4 1/2	8
LAD-FC-20	2	4 3/4	8 3/16	4 1/4	8 3/16	1 1/8	1 5/8	1 15/16	1 15/16	5	9
LAD-FC-25	2 1/2	6 1/4	11 3/16	5 3/4	11 3/16	1 5/8	2 1/8	2 15/16	2 9/16	6 1/2	12
LAD-FC-30	3	6 3/4	12 3/16	6 1/4	12 3/16	1 5/8	2 1/8	2 15/16	2 9/16	7	13




Standard Blade

Combo Blade



		
Open End (O)	End Cap	
X = 0	1 EC:	X = 0
	2 EC:	X = 0


LAD-FH CM

Model	S Slot Width	A Face Width	W1 Neck Width	B Border Width	H1 Height 1	H2 Height 2	Concealed Mount	
							W2 1 Slot	W2 2 Slot
LAD-FH-10	1	3 1/4	3 1/4	1 1/8	1 15/16	2 9/16	4	7
LAD-FH-15	1 1/2	3 3/4	3 3/4	1 1/8	1 15/16	2 9/16	4 1/2	8
LAD-FH-20	2	4 1/4	4 1/4	1 1/8	1 15/16	2 9/16	5	9
LAD-FH-25	2 1/2	5 3/4	5 3/4	1 5/8	1 15/16	2 9/16	6 1/2	12
LAD-FH-30	3	6 1/4	6 1/4	1 5/8	1 15/16	2 9/16	7	13



	
Open End (O)	End Cap
X = 0	1 EC: X = 0
	2 EC: X = 0



Model	S Slot Width	A Face Width	W1 Neck Width	B Border Width	H-1 Height 1	H-2 Height 2	Concealed Mount	
							W2 1 Slot	W2 2 Slot
LAD-GG-10	1	3 1/4	1 1/4	1 1/8	1 5/8	2 5/16	4	7
LAD-GG-15	1 1/2	3 3/4	1 3/4	1 1/8	1 5/8	2 5/16	4 1/2	8
LAD-GG-20	2	4 1/4	2 1/4	1 1/8	1 5/8	2 5/16	5	9
LAD-GG-25	2 1/2	5 3/4	2 3/4	1 5/8	2 1/2	2 15/16	6 1/2	12
LAD-GG-30	3	6 1/4	3 1/4	1 5/8	2 1/2	2 15/16	7	13