



Horizontal Blades

Frame Details



Aluminum




Steel

Product Features:

- Fixed roll-formed blades
- Aluminum construction (RG41-AL)
- Largest single section size is 48x48"
- Vertical or horizontal blade orientation
- Available in surface mount or lay-in border styles
- Oversized units made in multiple sections with mullion strips
- Steel construction (RG41-S)
- Fixed 0° or 40° blade deflection

Finishes

01 - White¹



03 - Black



¹ White Finish is suitable for a primer coat if field painting is required.

02 - Satin Silver




24 - Mill



28 - Custom Color




Product Pressure Drop Performance



Optional Accessories:



OBD - Steel Opposed Blade Damper
OBDA - Aluminum Opposed Blade Damper



L9 - Equalizing Grid (Square / Rect)
G3 - Equalizing Grid (Round)




PF - Sidewall Plaster Frame




TBPF - T-Bar Plaster Frame




LIPF - Lay-In Plaster Frame




TR - Square to Round Transition




TR-Deep - Deep Transition




Side View




Face View




Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.



Side View




Face View




Module Table	
12x12	
24x12	
24x24	
48x24	


Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.






Side View



Face View



Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.


Side View

Face View


Module Table	
12x12	
24x12	
24x24	
48x24	

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.