







Product Features:

- 51% free area perforated metal face panel
- Available in surface mount or lay-in border styles
- Oversized units made in multiple sections with mullion strips
- Steel construction (RGPF-S)
- Largest single section size is 48x48"
- Aluminum construction (RGPF-AL)








Finishes


01 - White ¹	03 - Black	¹ White Finish is suitable for a primer coat if field painting is required.
		
02 - Satin Silver	24 - Mill	
		
28 - Custom Color		
		

Product Pressure Drop Performance




Optional Accessories:


- | | |
|---|--|
|  | OBD - Steel Opposed Blade Damper
OBDA - Aluminum Opposed Blade Damper |
|  | L9 - Equalizing Grid (Square / Rect)
G3 - Equalizing Grid (Round) |
|  | PF - Sidewall Plaster Frame |
|  | TBPF - T-Bar Plaster Frame |
|  | LIPF - Lay-In Plaster Frame |
|  | TR - Square to Round Transition |
|  | TR-Deep - Deep Transition |



Face View




Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a $\frac{1}{2}$ " sphere can not pass.



Face View

Module Table
12x12
24x12
24x24
48x24
48x48

Face View



Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.