



### Product Features:

- Available for straight and curved applications
- Model LAD is available in slot widths from 1" to 3" wide
- Available with 1 or 2 slots
- Longest single section is 96"
- Various frame types are available for different applications:
  - AA Frame – Exposed Flange
  - CC Frame – Concealed Tape and Spackle
  - FF Frame – Flush Channel Frame
  - FH Frame – Offset Flush Frame
  - GG Frame – Beveled Frame
- Can come with hanger brackets for concealed mounting
- Available with standard or combo blade pattern controllers for horizontal or vertical applications
- Combination frames are available when two different frames are required on a single linear

### Finishes

20 - White/Black



03 - Black



02 - Satin Silver



24 - Mill




28 - Custom Color




<sup>1</sup> White Finish is suitable for a primer coat if field painting is required.

### Optional Accessories:




Standard Blades




Combo Blades





### CFD Throw Pattern Visualization

Horizontal Throw





Vertical Throw





**Standard Blade**

**Combo Blades**



| Open End (O) | End Cap |       | End Border |                    | Mitered Border |                    |
|--------------|---------|-------|------------|--------------------|----------------|--------------------|
| X = 0        | 1 EC:   | X = 0 | 1 EB:      | $X = \frac{3}{4}$  | MO:            | $X = \frac{3}{4}$  |
|              | 2 EC:   | X = 0 | 2 EB:      | $X = 1\frac{1}{2}$ | MM:            | $X = 1\frac{1}{2}$ |


**LAD-AA CM**

|           |            | Face Width |         | Neck Width |         |              |              |        | Concealed Mount |        |
|-----------|------------|------------|---------|------------|---------|--------------|--------------|--------|-----------------|--------|
| Model     | S          | A          | A       | W1         | W1      | B            | CB           | H      | W2              | W2     |
|           | Slot Width | 1 Slot     | 2 Slot  | 1 Slot     | 2 Slot  | Border Width | Border Width | Height | 1 Slot          | 2 Slot |
| LAD-AA-10 | 1          | 4 1/4      | 7 3/16  | 3 1/4      | 6 3/16  | 1 5/8        | 1 15/16      | 2      | 4               | 7      |
| LAD-AA-15 | 1 1/2      | 4 3/4      | 8 3/16  | 3 3/4      | 7 3/16  | 1 5/8        | 1 15/16      | 2      | 4 1/2           | 8      |
| LAD-AA-20 | 2          | 5 1/4      | 9 3/16  | 4 1/4      | 8 3/16  | 1 5/8        | 1 15/16      | 2      | 5               | 9      |
| LAD-AA-25 | 2 1/2      | 6 3/4      | 12 3/16 | 5 3/4      | 11 3/16 | 2 1/8        | 2 15/16      | 2 1/2  | 6 1/2           | 12     |
| LAD-AA-30 | 3          | 7 1/4      | 13 3/16 | 6 1/4      | 12 3/16 | 2 1/8        | 2 15/16      | 2 1/2  | 7               | 13     |






| Open End (O) | End Cap |       | End Border |                    | Mitered Border |                    |
|--------------|---------|-------|------------|--------------------|----------------|--------------------|
| X = 0        | 1 EC:   | X = 0 | 1 EB:      | $X = \frac{3}{4}$  | MO:            | $X = \frac{3}{4}$  |
|              | 2 EC:   | X = 0 | 2 EB:      | $X = 1\frac{1}{2}$ | MM:            | $X = 1\frac{1}{2}$ |




**LAD-AC CM**





|           |            | Face Width |         | Neck Width |         |              |              |        | Concealed Mount |        |
|-----------|------------|------------|---------|------------|---------|--------------|--------------|--------|-----------------|--------|
| Model     | S          | A          | A       | W1         | W1      | B            | CB           | H      | W2              | W2     |
|           | Slot Width | 1 Slot     | 2 Slot  | 1 Slot     | 2 Slot  | Border Width | Border Width | Height | 1 Slot          | 2 Slot |
| LAD-AC-10 | 1          | 4 1/4      | 7 3/16  | 3 1/4      | 6 3/16  | 1 5/8        | 1 15/16      | 2      | 4               | 7      |
| LAD-AC-15 | 1 1/2      | 4 3/4      | 8 3/16  | 3 3/4      | 7 3/16  | 1 5/8        | 1 15/16      | 2      | 4 1/2           | 8      |
| LAD-AC-20 | 2          | 5 1/4      | 9 3/16  | 4 1/4      | 8 3/16  | 1 5/8        | 1 15/16      | 2      | 5               | 9      |
| LAD-AC-25 | 2 1/2      | 6 3/4      | 12 3/16 | 5 3/4      | 11 3/16 | 2 1/8        | 2 15/16      | 2 1/2  | 6 1/2           | 12     |
| LAD-AC-30 | 3          | 7 1/4      | 13 3/16 | 6 1/4      | 12 3/16 | 2 1/8        | 2 15/16      | 2 1/2  | 7               | 13     |





**Standard Blade**






**Combo Blades**

| <br>Open End (O) | <br>End Cap |             | <br>End Border |             | <br>Mitered Border |                 |
|---------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|-------------|--------------------------------------------------------------------------------------------------|-------------|-------------------------------------------------------------------------------------------------------|-----------------|
|                                                                                                   | X = 0                                                                                        | 1 EC: X = 0 | 1 EB: X = 3/4                                                                                    | MO: X = 3/4 | 2 EC: X = 0                                                                                           | 2 EB: X = 1 1/2 |
|                                                                                                   |                                                                                              |             |                                                                                                  |             |                                                                                                       |                 |




**LAD-CC CM**



|           |            | Face Width |         | Neck Width |         |              |              |        | Concealed Mount |        |
|-----------|------------|------------|---------|------------|---------|--------------|--------------|--------|-----------------|--------|
| Model     | S          | A          | A       | W1         | W1      | B            | CB           | H      | W2              | W2     |
|           | Slot Width | 1 Slot     | 2 Slot  | 1 Slot     | 2 Slot  | Border Width | Border Width | Height | 1 Slot          | 2 Slot |
| LAD-CC-10 | 1          | 4 1/4      | 7 3/16  | 3 1/4      | 6 3/16  | 1 5/8        | 1 15/16      | 2      | 4               | 7      |
| LAD-CC-15 | 1 1/2      | 4 3/4      | 8 3/16  | 3 3/4      | 7 3/16  | 1 5/8        | 1 15/16      | 2      | 4 1/2           | 8      |
| LAD-CC-20 | 2          | 5 1/4      | 9 3/16  | 4 1/4      | 8 3/16  | 1 5/8        | 1 15/16      | 2      | 5               | 9      |
| LAD-CC-25 | 2 1/2      | 6 3/4      | 12 3/16 | 5 3/4      | 11 3/16 | 2 1/8        | 2 15/16      | 2 1/2  | 6 1/2           | 12     |
| LAD-CC-30 | 3          | 7 1/4      | 13 3/16 | 6 1/4      | 12 3/16 | 2 1/8        | 2 15/16      | 2 1/2  | 7               | 13     |





**Standard Blade**




**Combo Blade**



|                                                                                   |                                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
|  |  |
| Open End (O)                                                                      | End Cap                                                                           |
| X = 0                                                                             | 1 EC: X = 0                                                                       |
|                                                                                   | 2 EC: X = 0                                                                       |





**LAD-FF CM**


|           |            | Face Width |         | Neck Width |         |              |              |         | Concealed Mount |        |
|-----------|------------|------------|---------|------------|---------|--------------|--------------|---------|-----------------|--------|
| Model     | S          | A          | A       | W1         | W1      | B            | CB           | H       | W2              | W2     |
|           | Slot Width | 1 Slot     | 2 Slot  | 1 Slot     | 2 Slot  | Border Width | Border Width | Height  | 1 Slot          | 2 Slot |
| LAD-FF-10 | 1          | 3 1/4      | 6 3/16  | 3 1/4      | 6 3/16  | 1 1/8        | 1 15/16      | 1 15/16 | 4               | 7      |
| LAD-FF-15 | 1 1/2      | 3 3/4      | 7 3/16  | 3 3/4      | 7 3/16  | 1 1/8        | 1 15/16      | 1 15/16 | 4 1/2           | 8      |
| LAD-FF-20 | 2          | 4 1/4      | 8 3/16  | 4 1/4      | 8 3/16  | 1 1/8        | 1 15/16      | 1 15/16 | 5               | 9      |
| LAD-FF-25 | 2 1/2      | 5 3/4      | 11 3/16 | 5 3/4      | 11 3/16 | 1 5/8        | 2 15/16      | 2 9/16  | 6 1/2           | 12     |
| LAD-FF-30 | 3          | 6 1/4      | 12 3/16 | 6 1/4      | 12 3/16 | 1 5/8        | 2 15/16      | 2 9/16  | 7               | 13     |







|                                                                                   |                                                                                   |       |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------|
|  |  |       |
| <b>Open End (O)</b>                                                               | <b>End Cap</b>                                                                    |       |
| X = 0                                                                             | 1 EC:                                                                             | X = 0 |
|                                                                                   | 2 EC:                                                                             | X = 0 |





|           |            | Face Width |         | Neck Width |          |        |        |              |         | Concealed Mount |        |
|-----------|------------|------------|---------|------------|----------|--------|--------|--------------|---------|-----------------|--------|
| Model     | S          | A          | A       | W1         | W1       | B      | C      | CB           | H       | W2              | W2     |
|           | Slot Width | 1 Slot     | 2 Slot  | 1 Slot     | 2 Slot   | F Face | A Face | Border Width | Height  | 1 Slot          | 2 Slot |
| LAD-FA-10 | 1          | 3 3/4      | 6 3/16  | 3 1/4      | 5 11/16  | 1 1/8  | 1 5/8  | 1 15/16      | 1 15/16 | 4               | 7      |
| LAD-FA-15 | 1 1/2      | 4 1/4      | 7 3/16  | 3 3/4      | 6 11/16  | 1 1/8  | 1 5/8  | 1 15/16      | 1 15/16 | 4 1/2           | 8      |
| LAD-FA-20 | 2          | 4 3/4      | 8 3/16  | 4 1/4      | 7 11/16  | 1 1/8  | 1 5/8  | 1 15/16      | 1 15/16 | 5               | 9      |
| LAD-FA-25 | 2 1/2      | 6 1/4      | 11 3/16 | 5 3/4      | 11 11/16 | 1 5/8  | 2 1/8  | 2 15/16      | 2 9/16  | 6 1/2           | 12     |
| LAD-FA-30 | 3          | 6 3/4      | 12 3/16 | 6 1/4      | 12 11/16 | 1 5/8  | 2 1/8  | 2 15/16      | 2 9/16  | 7               | 13     |




|                                                                                   |                                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
|  |  |
| Open End (O)                                                                      | End Cap                                                                           |
| X = 0                                                                             | 1 EC: X = 0                                                                       |
|                                                                                   | 2 EC: X = 0                                                                       |





|           |            | Face Width |         | Neck Width |         |        |        |              |         | Concealed Mount |        |
|-----------|------------|------------|---------|------------|---------|--------|--------|--------------|---------|-----------------|--------|
| Model     | S          | A          | A       | W1         | W1      | B      | C      | CB           | H       | W2              | W2     |
|           | Slot Width | 1 Slot     | 2 Slot  | 1 Slot     | 2 Slot  | F Face | C Face | Border Width | Height  | 1 Slot          | 2 Slot |
| LAD-FC-10 | 1          | 3 3/4      | 6 3/16  | 3 1/4      | 6 3/16  | 1 1/8  | 1 5/8  | 1 15/16      | 1 15/16 | 4               | 7      |
| LAD-FC-15 | 1 1/2      | 4 1/4      | 7 3/16  | 3 3/4      | 7 3/16  | 1 1/8  | 1 5/8  | 1 15/16      | 1 15/16 | 4 1/2           | 8      |
| LAD-FC-20 | 2          | 4 3/4      | 8 3/16  | 4 1/4      | 8 3/16  | 1 1/8  | 1 5/8  | 1 15/16      | 1 15/16 | 5               | 9      |
| LAD-FC-25 | 2 1/2      | 6 1/4      | 11 3/16 | 5 3/4      | 11 3/16 | 1 5/8  | 2 1/8  | 2 15/16      | 2 9/16  | 6 1/2           | 12     |
| LAD-FC-30 | 3          | 6 3/4      | 12 3/16 | 6 1/4      | 12 3/16 | 1 5/8  | 2 1/8  | 2 15/16      | 2 9/16  | 7               | 13     |





**Standard Blade**






**Combo Blade**



|                                                                                   |                                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
|  |  |
| <b>Open End (O)</b>                                                               | <b>End Cap</b>                                                                    |
| X = 0                                                                             | 1 EC: X = 0                                                                       |
|                                                                                   | 2 EC: X = 0                                                                       |





**LAD-FH CM**

| Model     | S<br>Slot<br>Width | A<br>Face<br>Width | W1<br>Neck<br>Width | B<br>Border<br>Width | H1<br>Height 1 | H2<br>Height 2 | Concealed Mount |              |
|-----------|--------------------|--------------------|---------------------|----------------------|----------------|----------------|-----------------|--------------|
|           |                    |                    |                     |                      |                |                | W2<br>1 Slot    | W2<br>2 Slot |
| LAD-FH-10 | 1                  | 3 1/4              | 3 1/4               | 1 1/8                | 1 15/16        | 2 9/16         | 4               | 7            |
| LAD-FH-15 | 1 1/2              | 3 3/4              | 3 3/4               | 1 1/8                | 1 15/16        | 2 9/16         | 4 1/2           | 8            |
| LAD-FH-20 | 2                  | 4 1/4              | 4 1/4               | 1 1/8                | 1 15/16        | 2 9/16         | 5               | 9            |
| LAD-FH-25 | 2 1/2              | 5 3/4              | 5 3/4               | 1 5/8                | 1 15/16        | 2 9/16         | 6 1/2           | 12           |
| LAD-FH-30 | 3                  | 6 1/4              | 6 1/4               | 1 5/8                | 1 15/16        | 2 9/16         | 7               | 13           |



|                                                                                   |                                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
|  |  |
| <b>Open End (O)</b>                                                               | <b>End Cap</b>                                                                    |
| X = 0                                                                             | 1 EC: X = 0                                                                       |
|                                                                                   | 2 EC: X = 0                                                                       |



| Model     | S<br>Slot<br>Width | A<br>Face<br>Width | W1<br>Neck<br>Width | B<br>Border<br>Width | H-1<br>Height 1 | H-2<br>Height 2 | Concealed Mount |              |
|-----------|--------------------|--------------------|---------------------|----------------------|-----------------|-----------------|-----------------|--------------|
|           |                    |                    |                     |                      |                 |                 | W2<br>1 Slot    | W2<br>2 Slot |
| LAD-GG-10 | 1                  | 3 1/4              | 3 1/4               | 1 1/8                | 1 5/8           | 2 5/16          | 4               | 7            |
| LAD-GG-15 | 1 1/2              | 3 3/4              | 3 3/4               | 1 1/8                | 1 5/8           | 2 5/16          | 4 1/2           | 8            |
| LAD-GG-20 | 2                  | 4 1/4              | 4 1/4               | 1 1/8                | 1 5/8           | 2 5/16          | 5               | 9            |
| LAD-GG-25 | 2 1/2              | 5 3/4              | 5 3/4               | 1 5/8                | 2 1/2           | 2 15/16         | 6 1/2           | 12           |
| LAD-GG-30 | 3                  | 6 1/4              | 6 1/4               | 1 5/8                | 2 1/2           | 2 15/16         | 7               | 13           |