


PERFORMANCE

IN. W.G. (PA)	0.2 (50) CFM (L/s)	0.3 (75) CFM (L/s)	0.4 (100) CFM (L/s)	0.5 (125) CFM (L/s)	0.6 (150) CFM (L/s)	0.7 (175) CFM (L/s)	0.8 (200) CFM (L/s)	0.9 (225) CFM (L/s)
Net Supply Airflow	286 (135)	278 (131)	271 (128)	263 (124)	254 (120)	246 (116)	237 (112)	229 (108)
Gross Supply Airflow	290 (137)	282 (133)	273 (129)	265 (125)	259 (122)	250 (118)	239 (113)	231 (109)
Gross Exhaust Airflow	284 (134)	278 (131)	271 (128)	263 (124)	256 (121)	248 (117)	239 (113)	231 (109)

Sensible Effectiveness (ASE) @ 64 CFM (30 L/s)	32°F (0°C)	85%
Sensible Efficiency (SRE) @ 64 CFM (30 L/s)	32°F (0°C)	77%
Total Efficiency (TRE) @ 65 CFM (30 L/s)	95°F (35°C)	49%
Sensible Efficiency (SRE) @ 74 CFM (35 L/s)	-13°F (-25°C)	56%



ELECTRICAL SPECIFICATIONS	
VAC @ 60Hz	120
Watts @ 64 CFM (30L/s)	30
Amp Rating	4.5

WEIGHT:
57 LBS (25.8 KG)
SHIPPING WEIGHT:
67 LBS (30 KG)

NOTE:
 Front clearance of 25 in. (635 mm) is recommended for servicing unit. All ducts use 6 in. (152 mm) oval collars, balancing dampers are located on all collars.

MERV 13 Upgrade: 485467

