

SV5375

Louver Screen | Extruded Aluminum

Standard Construction

Material	Extruded 6063-T5 aluminum
Stationary Blade	0.081 in. (2.06 mm)
Vertical Support	Extruded aluminum Z support
Louver Screen Depth	4 in. (101.6 mm)
Free area - 4 ft. x 4 ft.	5.65 sq. ft. (0.52 sq m)
Percent Free Area	35%



Airolite Louver Screen Type SV5375 is a versatile, inverted, vertical blade, 5.375 inch (136.5 mm) deep architectural louver screen designed for applications that require economical sight barriers. The vertical louver screen blade profile provides an effective visual screen when viewed from any angle. All materials are available in Airolite's broad array, kynar/fluoropolymer, coatings for durability and compatibility with adjacent materials and finishes. Please contact your local Airolite representative or the factory for assistance with the layout and design of supports systems when required.

GENERAL

Where indicated on plans or described in schedules, furnish and install Louver Screen Type SV5375 as designed and manufactured by The Airolite Company LLC, Schofield, Wisconsin. Louver screens shall be furnished in the configuration represented on the plan drawings and shall include installation hardware and finishes as specified and required as required for a complete installation.

SUBMITTALS

Manufacturer shall submit shop drawings incorporating key plans, elevations, sections and details showing profiles, angles and spacing of louver screen blades and frames; unit dimensions related to wall openings and construction; and anchorage details and locations. Submit theoretical calculations prepared by a professional engineer specializing in the application of welding technology demonstrating that each fillet weld joining blade and frame members will withstand a minimum of 526 pounds of force in shear. Provide samples of manufacturer's finish and color charts showing the full range of colors available.

PRODUCTS

Louver screens shall be inverted, horizontal blade, Louver Screen Type SV5375 with concealed vertical mullions. Louver screens shall be 5.375 inches (136.5mm) deep and assembled by mechanically fastening or welding extruded aluminum components. Blades shall be 0.081-inch (2.06 mm) thick extruded aluminum, alloy 6005-T5. Blades shall be vertical, sight proof and spaced 4.250 inches (108 mm) on center. Blades shall be secured to horizontal support members located to withstand the specified wind design load.

STRUCTURAL DESIGN CRITERIA

Manufacturer shall design and furnished all supports required to withstand a wind force of not less than 25 pounds per square foot. Louver screens larger than 72-inches (183 cm) wide x 144-inches (366 cm) high or 144-inches (366 cm) wide x 72-inches (183 cm) high will be fabricated and installed in multiples sections. Louver screen blades, horizontal members and anchorages shall be demonstrated to withstand the specified wind design load.

Document Links

[Grilles & Screens](#)

[Finishes & Colors](#)

[Airolite Warranty Statement](#)

Standard Details

[SV5375 Standard Details](#)

