


# PERFORMANCE

IN. W.G. (PA)	0.2 (50) CFM (L/s)	0.3 (75) CFM (L/s)	0.4 (100) CFM (L/s)	0.5 (125) CFM (L/s)	0.6 (150) CFM (L/s)	0.7 (175) CFM (L/s)	0.8 (200) CFM (L/s)	0.9 (225) CFM (L/s)
Net Supply Airflow	123 (58)	117 (55)	108 (51)	97 (46)	87 (41)	74 (35)	57 (27)	40 (19)
Gross Supply Airflow	125 (59)	119 (56)	110 (52)	100 (47)	89 (42)	74 (35)	59 (28)	40 (19)
Gross Exhaust Airflow	121 (57)	117 (55)	110 (52)	104 (49)	93 (44)	78 (37)	57 (27)	28 (13)

ELECTRICAL SPECIFICATIONS	
VAC @ 60Hz	120
Watts / Low Speed	22
Watts / High Speed	50
Amp Rating	1.4

Sensible Effectiveness (ASE) @ 50 CFM (23 L/s)	32°F (0°C)	81%
Sensible Efficiency (SRE) @ 64 CFM (30 L/s)	32°F (0°C)	71%
Sensible Efficiency (SRE) @ 49 CFM (23 L/s)	32°F (0°C)	73%
Total Efficiency (TRE) @ 49 CFM (23 L/s)	95°F (35°C)	52%



WEIGHT:  
**34 LBS (15.5 KG)**

SHIPPING WEIGHT:  
**36 LBS (16 KG)**

## NOTE:

Front clearance of 25 in. (635 mm) is recommended for servicing unit. All ducts use 5 in. (125 mm) round collars.

MERV 13 Upgrade: 485463

