


# PERFORMANCE

IN. W.G. (PA)	0.2 (50) CFM (L/s)	0.3 (75) CFM (L/s)	0.4 (100) CFM (L/s)	0.5 (125) CFM (L/s)	0.6 (150) CFM (L/s)	0.7 (175) CFM (L/s)	0.8 (200) CFM (L/s)	0.9 (225) CFM (L/s)
Net Supply Airflow	191 (90)	184 (87)	176 (83)	167 (79)	159 (75)	150 (71)	140 (66)	133 (63)
Gross Supply Airflow	193 (91)	186 (88)	178 (84)	170 (80)	159 (75)	150 (71)	142 (67)	133 (63)
Gross Exhaust Airflow	201 (95)	193 (91)	184 (87)	176 (83)	167 (79)	159 (75)	148 (70)	140 (66)

WATTSCFM

Sensible Effectiveness (ASE) @ 64 CFM (30 L/s)	32°F (0°C)	88%	0.44
Sensible Efficiency (SRE) @ 64 CFM (30 L/s)	32°F (0°C)	84%	0.44
Sensible Efficiency (SRE) @ 72 CFM (34 L/s)	-13°F (-25°C)	62%	0.40
Total Efficiency (TRE) @ 64 CFM (30 L/s)	95°F (35°C)	60%	0.50



ELECTRICAL SPECIFICATIONS	
VAC @ 60Hz	120
Watts @ 64 CFM (30 L/s)	28
Amp Rating	2.0

**WEIGHT:**  
**42 LBS (19 KG)**

**SHIPPING WEIGHT:**  
**44 LBS (20 KG)**

**NOTE:**  
 Front clearance of 22 in. (559 mm) is recommended for servicing unit. All ducts use 6 in. (152 mm) round collars.

MERV 13 Upgrade: 485465

