



Product Features:


- Available with 1" wide frames
- Available with 7/32" or 1/8" thick bars
- Pencil proof 17/64" bars available
- Available with 1/2" or 1/4" bar spacing
- Widths 3.5" and smaller use flap style dampers
- Widths 4" and larger use standard opposed blade dampers
- Available for straight and curved applications
- Various frame types are available for different applications
 - H - Concealed Mounting Hanger
 - F - Floor Mounting
 - FP - Floor Mounting Pencil Proof
 - TS - Tape & Spackle
- Available in lengths up to 1200" in multiple sections.
- Max. Single Section Length 72"
Model LBG is available in widths from 1 1/2" to 24" in 1/2" increments
- Can come with hanger brackets for concealed mounting
- Available with sub-frames for specific applications
- Extruded aluminum construction

Finishes




¹ White Finish is suitable for a primer coat if field painting is required.


CFD Throw Pattern Visualization



Optional Accessories:




L9 - Equalizing Grid




DA - Opposed Blade Damper Aluminum



PP - Pencil Proof Core
17/64" Pencil Proof Bars




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2







Open / Open	
Length	L = 1/2




Mitered / Open	
Length	L = 3/4








End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4






End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0









Mitered / Open	
Length	L = 3/4





Available Lengths	
Min	1 1/2
Max	24







Available Lengths	
Min	1 1/2
Max	24

Side View


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2





Open / Open	
Length	L = 0



Mitered / Open	
Length	L = 3/4







Available Lengths	
Min	1 1/2
Max	24

Side View


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4






End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 2 3/4




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 1 3/8




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4





0° Deflection



15° Deflection







30° Deflection




Available Lengths	
Min	1 1/2
Max	24

Side View


*Available in 1/2 increments




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 2 3/4




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 1 3/8




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4





0° Deflection



15° Deflection




30° Deflection




Available Lengths	
Min	1 1/2
Max	24

Side View


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 1 1/2




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 3/4




0° Deflection




15° Deflection



30° Deflection




End View




Side View

Available Lengths	
Min	1 1/2
Max	24


*Available in 1/2 increments




Mitered / Mitered	
Length	L = 2 3/4




Open / Open	
Length	L = 0




Mitered / Open	
Length	L = 1 3/8




0° Deflection




15° Deflection



30° Deflection



Note: Generic "Linear Bar Grille" shown for reference



Note: Generic "Linear Bar Grille" shown for reference