


Product Features:

- Model SD41/42-C offers a curved frame style
- SD41-C is single deflection with one set of adjustable blades
- Units can come with air scoop for airflow adjustment
- Front blades are vertically oriented, with optional rear blades running horizontally
- SD42-C is double deflection with two set of adjustable blades
- Curved frame is designed to fit a specific duct diameter and match the curvature
- All aluminum construction
- Features foam gasket to provide a tight fit onto round duct work

Finishes
01 - White¹

03 - Black



¹ White Finish is suitable for a primer coat if field painting is required.





02 - Satin Silver 04 - Clear Anodized




28 - Custom Color




24 - Mill


CFD Throw Pattern Visualization

Optional Accessories:

OBDE - Extruded Aluminum
 Opposed Blade Damper

OBDA - Aluminum
 Opposed Blade Damper




* Air Scoop is Standard construction on Supply Only




Face View **End View**


Curved Flange Table		
Listed Height	Duct Diameter Range (inches)	
	Minimum	Maximum
3	6	16
4	8	36
6	10	36
8	10	36
10	14	36
12	16	36



* Air Scoop is Standard construction on Supply Only



Face View



End View

Curved Flange Table		
Listed Height	Duct Diameter Range (inches)	
	Minimum	Maximum
3	6	16
4	8	36
6	10	36
8	10	36
10	14	36
12	16	36