




Product Features:


- Universal Plenums can be used with any linear diffuser or linear bar grille model
- Model UP-LAD, UP-LSD, UP-LBG also available with optional insulation
- Beaded inlet collars enable a simplified duct connection
- Optional dampers can be included to control the airflow
- Standard insulation on UPI is 1/2" Internal Fiberglass with other options available
- External fiberglass insulation (EI)
- Internal closed cell foam (CC) insulation
- Standard inlet sizes are 6" (round) or 8", 10", 12" and 14" (oval)
- Standard lengths available are 24", 36", 48", 60" and 72".
- Standard Galvanized Steel Construction

Optional Accessories:



LQ - Locking Quadrant




ID - Inlet Damper




ROD - Remote Operated Damper




FODR - Face-Operated Damper Rod




Plenum (Installed) End View



Plenum Side View



1 SLOT




2 SLOTS


Length
L
24
36
48
60
72

Inlet Chart			
Size	Type	A	B
6	Round	5 7/8	-
7	Oval	5 7/8	7 1/4
8	Oval	5 7/8	8 3/8
9	Oval	5 7/8	10
10	Oval	5 7/8	11 9/16
12	Oval	5 7/8	14 13/16
14	Oval	5 7/8	17 13/16


		Neck Width			
Model	S	W1		W2	
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot
UP-LAD-10	1	3 1/4	6 3/16	2 1/4	5 3/16
UP-LAD-15	1 1/2	3 3/4	7 3/16	2 3/4	6 3/16
UP-LAD-20	2	4 1/4	8 3/16	3 1/4	7 3/16
UP-LAD-25	2 1/2	5 3/4	11 3/16	4 3/4	10 3/16
UP-LAD-30	3	6 1/4	12 3/16	5 1/4	11 3/16



Plenum (Installed) End View



Plenum Side View




1 SLOT

2 SLOTS


Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	


Model	S	W	W
	Slot Width	Width 1-Slot	Width 2-Slot
UP-LAD-10 CM	1	4	7
UP-LAD-15 CM	1 1/2	4 1/2	8
UP-LAD-20 CM	2	5	9
UP-LAD-25 CM	2 1/2	6 1/2	12
UP-LAD-30 CM	3	7	13




Plenum (Installed) End View



Plenum Side View



1 SLOT




2 SLOTS


Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	


Models	S	Number of Slots	W1	W2
	Slot Width		Width	
UP-LADTZ-4	1	1	3 1/4	2 1/4
UP-LADTZ-6	1	2	5 1/4	4 1/4



Plenum (Installed) End View




Plenum Side View




Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	


Models	S	Number of Slots	W W (Width)
	Slot Width		
UP-LADTZ-4 CM	1	1	4
UP-LADTZ-6 CM	1	2	6



Plenum (Installed) End View



Plenum Side View




1 SLOT

2 SLOTS


Length
L
24
36
48
60
72

Inlet Chart			
Size	Type	A	B
6	Round	5 7/8	-
7	Oval	5 7/8	7 1/4
8	Oval	5 7/8	8 3/8
9	Oval	5 7/8	10
10	Oval	5 7/8	11 9/16
12	Oval	5 7/8	14 13/16
14	Oval	5 7/8	17 13/16


		Neck Width			
Model	S	W1		W2	
	Slot Width	1 Slot	2 Slot	1 Slot	2 Slot
UP-LAD-10	1	3 1/4	6 3/16	2 1/4	5 3/16
UP-LAD-15	1 1/2	3 3/4	7 3/16	2 3/4	6 3/16
UP-LAD-20	2	4 1/4	8 3/16	3 1/4	7 3/16
UP-LAD-25	2 1/2	5 3/4	11 3/16	4 3/4	10 3/16
UP-LAD-30	3	6 1/4	12 3/16	5 1/4	11 3/16



Plenum (Installed) End View




Plenum Side View




Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	


Model	S	W	W
	Slot Width	Width 1-Slot	Width 2-Slot
UP-LAD-10 CM	1	4	7
UP-LAD-15 CM	1 1/2	4 1/2	8
UP-LAD-20 CM	2	5	9
UP-LAD-25 CM	2 1/2	6 1/2	12
UP-LAD-30 CM	3	7	13




Plenum (Installed) End View



Plenum Side View



1 SLOT




2 SLOTS


Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	


Models	S	Number of Slots	W1	W2
	Slot Width		Width	
UP-LADTZ-4	1	1	3 1/4	2 1/4
UP-LADTZ-6	1	2	5 1/4	4 1/4



Plenum (Installed) End View




Plenum Side View




Length L	Inlet Chart			
	Size	Type	A	B
24	6	Round	5 7/8	-
36	7	Oval	5 7/8	7 1/4
48	8	Oval	5 7/8	8 3/8
60	9	Oval	5 7/8	10
72	10	Oval	5 7/8	11 9/16
	12	Oval	5 7/8	14 13/16
	14	Oval	5 7/8	17 13/16


Models	S Slot Width	Number of Slots	W W (Width)
UP-LADTZ-4 CM	1	1	4
UP-LADTZ-6 CM	1	2	6



Plenum (Installed) End View



Plenum Side View




Section View

Available Widths	
Min	1 1/2
Max	24


*Available in 1/2 increments

Length
L
24
36
48
60
72


Inlet Chart			
Size	Type	A	B
6	Round	5 7/8	-
7	Oval	5 7/8	7 1/4
8	Oval	5 7/8	8 3/8
9	Oval	5 7/8	10
10	Oval	5 7/8	11 9/16
12	Oval	5 7/8	14 13/16
14	Oval	5 7/8	17 13/16



Plenum (Installed) End View



Plenum Side View




Section View

Available Widths	
Min	$1\frac{1}{2}$
Max	24


*Available in 1/2 increments

Length
L
24
36
48
60
72


Inlet Chart			
Size	Type	A	B
6	Round	$5\frac{7}{8}$	-
7	Oval	$5\frac{7}{8}$	$7\frac{1}{4}$
8	Oval	$5\frac{7}{8}$	$8\frac{3}{8}$
9	Oval	$5\frac{7}{8}$	10
10	Oval	$5\frac{7}{8}$	$11\frac{9}{16}$
12	Oval	$5\frac{7}{8}$	$14\frac{13}{16}$
14	Oval	$5\frac{7}{8}$	$17\frac{13}{16}$



Plenum (Installed) End View




Plenum Side View




Length
L
24
36
48
60
72

Inlet Chart			
Size	Type	A	B
6	Round	5 7/8	-
7	Oval	5 7/8	7 1/4
8	Oval	5 7/8	8 3/8
9	Oval	5 7/8	10
10	Oval	5 7/8	11 9/16
12	Oval	5 7/8	14 13/16
14	Oval	5 7/8	17 13/16


Model	Neck Width								
	S	W							
	Slot Width	1 Slot	2 Slot	3 Slot	4 Slot	5 Slot	6 Slot	7 Slot	8 Slot
UP-LSD	1/2	2	3 1/2	4 1/2	6	7	8 1/2	9 1/2	11
UP-LSD	3/4	2 1/2	4	5 1/2	7	8 1/2	10	11 1/2	13
UP-LSD	1	2 1/2	4 1/2	6	8	9 1/2	11 1/2	13	15
UP-LSD	1 1/2	3	5 1/2	7 1/2	10	N/A	N/A	N/A	N/A



Plenum (Installed) End View




Plenum Side View




Length
L
24
36
48
60
72

Inlet Chart			
Size	Type	A	B
6	Round	5 7/8	-
7	Oval	5 7/8	7 1/4
8	Oval	5 7/8	8 3/8
9	Oval	5 7/8	10
10	Oval	5 7/8	11 9/16
12	Oval	5 7/8	14 13/16
14	Oval	5 7/8	17 13/16


Model	Neck Width								
	S	W							
	Slot Width	1 Slot	2 Slot	3 Slot	4 Slot	5 Slot	6 Slot	7 Slot	8 Slot
UP-LSD	1/2	2	3 1/2	4 1/2	6	7	8 1/2	9 1/2	11
UP-LSD	3/4	2 1/2	4	5 1/2	7	8 1/2	10	11 1/2	13
UP-LSD	1	2 1/2	4 1/2	6	8	9 1/2	11 1/2	13	15
UP-LSD	1 1/2	3	5 1/2	7 1/2	10	N/A	N/A	N/A	N/A




Plenum (Installed) End View




Plenum Side View




1 SLOT



2 SLOT



1 SLOT




2 SLOT

CONCEALED MOUNT (CM)


Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	


Tech Zone Width	Number of Slots	W (Width)
4	1	2 1/2
4	2	4
6	1	2 1/2
6	2	4
6	3	5 1/2
6	4	7




Plenum (Installed) End View




Plenum Side View




1 SLOT



2 SLOT



1 SLOT



2 SLOT

CONCEALED MOUNT (CM)

Length
L
24
36
48
60
72

Inlet Chart				
Size	Type	A	B	
6	Round	5 7/8	-	
7	Oval	5 7/8	7 1/4	
8	Oval	5 7/8	8 3/8	
9	Oval	5 7/8	10	
10	Oval	5 7/8	11 9/16	
12	Oval	5 7/8	14 13/16	
14	Oval	5 7/8	17 13/16	

Tech Zone Width	Number of Slots	W (Width)
4	1	2 1/2
4	2	4
6	1	2 1/2
6	2	4
6	3	5 1/2
6	4	7