


REVISION

SYM

3

ITEM:

1. UL CLASSIFIED AS BOTH A FIRE DAMPER AND A LEAKAGE RATED SMOKE DAMPER
1.1 1-1/2 HR. LABEL - FOR FIRE SEPARATIONS LESS THAN 3 HOURS.
2. UL QUALIFIED DAMPER/ACTUATOR ASSEMBLY (ELECTRIC)
3. RATED BARRIER
4. RETAINING PLATE
5. EXPANSION CLEARANCE
6. BREAKAWAY JOINT
7. STEEL DUCT
8. ACCESS DOOR (NFPA 80 AND 105)
9. UL LISTED HEAT RESPONSIVE DEVICE (RRL, RRL/OCI, TOR)



NOTE:

1. DAMPERS SHALL BE CONSTRUCTED, TESTED, LABELED AND INSTALLED IN ACCORDANCE WITH UL 555, UL 555S, NFPA 80, NFPA 90A, NFPA 92, NFPA 101, NFPA 105, AND DAMPER MANUFACTURER'S INSTALLATION INSTRUCTIONS.
2. RATED BARRIER SHALL MEET THE REQUIREMENTS OF INTERNATIONAL BUILDING CODE (IBC) AND COMPLY WITH LOCAL CODE REQUIREMENTS.
 - 2.1. DAMPERS SHALL BE RATED FOR VERTICAL OR HORIZONTAL MOUNTING AS REQUIRED AND SHOWN ON PROJECT PLANS.
3. DAMPER OPENING (EXPANSION GAPS) SHALL BE PER DAMPER MANUFACTURER'S UL APPROVED INSTALLATION INSTRUCTIONS.
 - 3.1. MAXIMUM DAMPER OPENING MAY NOT EXCEED THE DAMPER MANUFACTURER'S MAXIMUM UL LISTED SIZE.
4. SLEEVE GAUGE, TERMINATIONS AND RETAINING ANGLES SHALL BE AS REQUIRED AND COMPLY WITH UL AND SMACNA REQUIREMENTS.
5. HEAT RESPONSIVE DEVICE SHALL BE A SINGLE TEMPERATURE ELECTRIC HEAT SENSOR OR DUAL TEMPERATURE OVERRIDE SENSOR. CHECK PROJECT SPECIFIC REQUIREMENTS AND SPECIFICATIONS FOR TYPE AND TEMPERATURE RATINGS.
6. ACCESS DOORS SHALL BE PROVIDED FOR INSPECTION, TESTING AND MAINTENANCE TO COMPLY WITH NFPA 80 AND 105.
7. FSDR-511 MAY BE MOUNTED EITHER HORIZONTALLY OR VERTICALLY. BLADE AXIS MUST REMAIN WITHIN 30 DEGREES OF HORIZONTAL.
8. BASIS OF DESIGN SHALL BE GREENHECK FSDR-511 1-1/2 HOUR RATED STEEL ROUND COMBINATION FIRE SMOKE DAMPER. (ALTERNATE MODEL: SSFSDR-511 1-1/2 HOUR FIRE RATED)

Copyright © 2025 Greenheck Fan Corporation

Greenheck Fan Corporation reserves the right to make product changes without notice

PAINT	PART NO.	MAT'L	GAUGE	DESCRIPTION
				DRAWN BY ECO
				BERNETT
				DATE 10/29/2025
				ENG. REF.
				SUPERSEDES
				SCALE
				CAD DRAWING NO. 1/8
				B
				100563209