Technical data sheet GM24SR.1B

Damper actuator for adjusting dampers in technical building installations

- **Torque motor 360 in-lb [40 Nm]**
- **Nominal voltage AC/DC 24 V**
- **Control Modulating, On/Off, Floating point, Communicative via MP-Bus**
- **Running Time (Motor) 150 s (90...150 s)**
- **Communication via Belimo MP-Bus**
- **With pluggable connecting cable**
- **5-year warranty**



Picture may differ from product

Technical data

Electrical data	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...28.8 V / DC 19.2...28.8 V
	Power consumption in operation	2 W
	Power consumption in rest position	0.2 W
	Transformer sizing	5 VA
	Connection supply/control	Cable Plenum 3 ft. [1 m] 4x 0.5 mm² [21 AWG] with 1/2" NPT conduit connector
	Parallel operation	See Electrical Installation or contact your local Belimo representative
Data bus communication	Communicative control	MP-Bus
	Number of nodes	MP-Bus max. 16
Functional data	Torque motor	360 in-lb [40 Nm]
	Operating range Y	2...10 V
	Input impedance	100 kΩ
	Operating range Y variable	Start point 0.5...30 V End point 2.5...32 V
	Operating modes optional	On/Off Floating Point communicative
	Position feedback U	2...10 V
	Position feedback U note	Max. 1 mA
	Position feedback U variable	Start point 0.5...8 V End point 2.5...10 V
	Response sensitivity	1.0% of ΔU
	Reversal hysteresis	2.5% of ΔU
	Position accuracy	±5%
	Direction of motion motor	Y = 0 V: left end stop, position CW
	Direction of motion variable	electronically reversible
	Direction of motion note	selectable with Belimo Assistant 2
	Manual override	with lateral handle, can be locked
	Angle of rotation	Max. 95°
	Angle of rotation note	can be electronically limited on both sides with Belimo Assistant 2
	Running Time (Motor)	150 s / 90°
	Running time motor variable	90...150 s
	Sound power level motor	40 dB(A)
	Adaptation Setting Range	with Belimo Assistant 2

Technical data

Functional data	Override control	MIN (minimum position) = 0% MID (intermediate position, AC only) = 50% MAX (maximum position) = 100%
	Override control variable	MIN = 0%...(MAX – 20%) MID = MIN...MAX MAX = (MIN + 20%)...100%
	Mechanical interface	Universal shaft clamp reversible 0.47...1.05" [12...26.7 mm]
	Position indication	Mechanical
Safety data	Protection class IEC/EN	III, Protective Extra-Low Voltage (PELV)
	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 2
	Housing	UL Enclosure Type 2
	EMC	CE according to 2014/30/EU
	Certification IEC/EN	IEC/EN 60730-1 and IEC/EN 60730-2-14
	UL Approval	cULus according to UL60730-1, UL60730-2-14 and CAN/CSA E60730-1
	UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC
	Type of action	Type 1
	Rated impulse voltage supply / control	0.8 kV
	Pollution degree	3
	Environmental Conditions Operation	Class 3K23 according to IEC 60721-3-3
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-22...131°F [-30...55°C]
	Ambient temperature note	up to 140°F [60°C], max. 2 h/day
	Environmental Conditions Transport	Class 2K11 according to IEC 60721-3-2
	Transportation temperature	-40...176°F [-40...80°C]
	Environmental Conditions Storage	Class 1K21 according to IEC 60721-3-1
	Storage temperature	-22...131°F [-30...55°C]
	Servicing	maintenance-free
Weight	Weight	3.5 lb [1.6 kg]
Materials	Housing material	UL94-5VA

Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: Only possible if no (sea) water, snow, ice, sunlight, or aggressive gases directly act on the device, and if it is ensured that the ambient conditions remain within the limit values specified in the data sheet at all times.
- Only authorized specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- To calculate the torque required, the specifications supplied by the damper manufacturers concerning the cross-section and design, as well as the installation site and ventilation conditions, must be observed.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Product features

Operating mode

Conventional operation:

The actuator is connected with an analog control signal Y (note the operating range) and drives to the position defined. The measuring voltage U serves for the electrical display of the actuator position and as control signal for other actuators.

Operation on Bus:

The actuator receives its digital control signal from the higher level controller via the MP-Bus and drives to the position defined. Connection U serves as communication interface and does not supply an analogue measuring voltage.

Visual status display

The device indicates its operation by means of a green LED.

Converter for sensors

Connection option for an active sensor. The actuator serves as an analog/digital converter for the transmission of the sensor signal via MP-Bus to the higher-level system.

Additional material may be required for the sensor connection. See "Electrical accessories".

Configurable Device

The factory settings cover the most common applications.

Parameters can be modified using Belimo Assistant 2, either wirelessly via Near Field Communication (NFC), or via a wired connection.

Simple direct mounting

Simple direct mounting on the damper shaft with a universal shaft clamp, supplied with an anti-rotation mechanism to prevent the actuator from rotating.

Manual override

Manual override possible with lateral handle (the gear train is disengaged for as long as the handle is actuated or remains locked).

Manual override with stationary actuator is used for installation, commissioning and maintenance of the application.

Adjustable angle of rotation

Adjustable angle of rotation with electrical end stops. The setting of the control range (Min – Max) is made with Belimo Assistant 2.

For applications with mechanical end stops or an actual operating range of less than 95°, the control range must be adjusted or an adaptation carried out using Belimo Assistant 2.

High functional reliability

The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

Innovative motorization

The actuator uses the powerful Belimo M600 microchip in combination with the INFORM method. It provides the full starting torque from a standstill with high precision (sensorless INFORM-Drive by Prof. Schrödl).


Adaptation

An adaptation can be triggered with Belimo Assistant 2. During adaptation of a mounted actuator, both damper end stops on the system are detected (entire setting range).

The actuator then moves into the position defined by the control signal.

Connection

The cable can be plugged in and unplugged from the device.



Accessories

Tools	Description	Type
	Service tool for wired and wireless setup, on-site operation and troubleshooting.	Belimo Assistant 2
	Belimo Assistant Link Bluetooth and USB to NFC and MP-Bus converter for configurable and communicative devices	LINK.10
	Connecting cable 16 ft [5 m], A: RJ11 6/4 LINK.10, B: free wire end for connection to MP/PP terminal	ZK2-GEN

Electrical accessories	Description	Type
	Connecting terminal compl. for 24 V applications, with 1/2" NPT conduit connector	A.EIST.12
	Connecting cable for 24 V applications, 3 ft. [1 m] Plenum, 4x 0.5 mm²/ 20 AWG, with 1/2" NPT conduit connector	A.EISC.12
	Cable conduit connector, 1/2" NPT	S.EISCC.10
	Connecting terminal compl. 24 V	S.EIST.10
	Blind plug	S.EISBP.10

Mechanical accessories	Description	Type
	Position indicator	S.MISPI.10
	Baseplate extension for GM..A to GM..	Z-GMA
	Mounting kit for linkage operation for flat installation	ZG-GMA
		ZG-JSA-1

Electrical installation

Supply from isolating transformer.


Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.


The cable cross-section (mm²) must be determined on the basis of the actuator performance data (VA, W), the cable resistance, the number of actuators, and the total cable length according to electrotechnical principles. High voltage drops across the installation cables can affect the function of the actuator if, for example, the nominal voltage range (AC/DC) is not respected.

High voltage drops across the control signal and position feedback lines (Y/U) with respect to ground affect the signal values (0.5/2...10 V) and can change the actuator position.

Wire colors:
1 = black
2 = red
3 = white
5 = orange

AC/DC 24 V, modulating







Further electrical installations

Hardwired control with specific parameters

AC/DC 24 V, on/off



AC/DC 24 V, floating point




Functions with basic values (conventional mode)

MP-Bus network topology




There are no restrictions regarding the network topology (bus, star, ring or mixed forms are permitted).
Supply and communication in one and the same 3-wire cable
• no shielding or twisting necessary
• no terminating resistors required

Connection on the MP-Bus



Max. 16 MP-Bus nodes


Possibility of daisy-chain wiring



Additional material may be required for daisy-chain wiring.
See "Electrical accessories".

Sensor Connection

Connection with active sensor




Possible input voltage range:
0...10 V
Resolution 10 mV
To capture for example:
- Active temperature, humidity, and air quality sensors
- Pressure / differential pressure sensors


Further electrical installations

Alternative sensor connection

Connection with active sensor



Operating controls and indicators



1 **Manual override lever**
Rotate lever counterclockwise to end position:
- Gear train disengages, manual override possible

Return lever clockwise to starting position:
- Gear train engages, followed by standard mode

2 **Status display, LED green**

LED on:	operation OK
LED flashing:	Connect device with Belimo Assistant 2 for additional information
LED off:	No power supply

3 **NFC interface**

A **Port A**, see Electrical Installation

B **Port B**, see Electrical Installation

Service

Using Belimo Assistant 2, device parameters can be modified. Belimo Assistant 2 can operate on a smartphone, tablet, or PC. The available connection options vary depending on the hardware on which Belimo Assistant 2 is installed.

For more information about Belimo Assistant 2, refer to the Quick Guide – Belimo Assistant 2.

Service


Wireless connection


Belimo devices marked with the NFC logo can be accessed either directly with an NFC-capable smartphone or with a Bluetooth-capable smartphone connected to Belimo Assistant Link.

Requirement:

- NFC- or Bluetooth-capable smartphone or tablet
- Belimo Assistant 2 (Google Play and Apple App Store)

Align the NFC-capable smartphone or Belimo Assistant Link with the device's NFC logo so that both NFC antennas are superposed.







Wired connection

Belimo devices can be accessed by connecting Belimo Assistant Link to the USB port on a PC or laptop and to the service socket or MP-Bus wire on the device.


Belimo Assistant 2 acts as MP client. Therefore, no other MP client shall be connected to the device.







Dimensions

Shaft length

	Min. 2.05" [52 mm]
	Min. 0.75" [20 mm]

Clamping range





Further documentation

- Overview MP Cooperation Partners
- Tool connections
- Introduction to MP-Bus Technology
- Quick Guide – Belimo Assistant 2

Technical data sheet GMC24S.27

Damper actuator for adjusting dampers in technical building installations

- **Torque motor 40 Nm**
- **Nominal voltage AC/DC 24 V**
- **Control On/Off**
- **Running Time (Motor) 35 s (35...150 s)**
- **With two integrated auxiliary switches**
- **With pluggable connecting cable**
- **5-year warranty**
- **UL Listed device**



Picture may differ from product

Technical data

Electrical data	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...28.8 V / DC 19.2...28.8 V
	Power consumption in operation	4 W
	Power consumption in rest position	0.3 W
	Transformer sizing	8 VA
	Auxiliary switch	2x SPST (Single Pole, Single Throw)
	Switching capacity auxiliary switch	1 mA...1 A, AC/DC 5...30 V
	Switching points auxiliary switch	S1/S2: 10% / S4/S5: 90% (configurable with Belimo Assistant 2)
	Connection supply/control	Cable FRNC (halogen-free) 3 ft. [1 m] 4x 0.5 mm² [21 AWG] with 1/2" NPT conduit connector
	Connection auxiliary switch	Cable FRNC (halogen-free) 3 ft. [1 m] 4x 0.75 mm² [19 AWG] with 1/2" NPT conduit connector
	Parallel operation	See Electrical Installation or contact your local Belimo representative
Functional data	Torque motor	40 Nm
	Direction of motion motor	clockwise rotation (cw)
	Direction of motion note	selectable with Belimo Assistant 2
	Manual override	with lateral handle, can be locked
	Angle of rotation	Max. 95°
	Angle of rotation note	can be electronically limited on both sides with Belimo Assistant 2
	Running Time (Motor)	35 s / 90°
	Running time motor variable	35...150 s
	Sound power level motor	60 dB(A)
	Mechanical interface	Universal shaft clamp reversible 0.47...1.05" [12...26.7 mm]
	Position indication	Mechanical
Safety data	Protection class IEC/EN	III, Protective Extra-Low Voltage (PELV)
	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 2
	Housing	UL Enclosure Type 2
	EMC	CE according to 2014/30/EU
	Low voltage directive	CE according to 2014/35/EU
	Certification IEC/EN	IEC/EN 60730-1 and IEC/EN 60730-2-14

Technical data

Safety data	UL Approval	cULus according to UL60730-1, UL60730-2-14 and CAN/CSA E60730-1
	UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC
	Type of action	Type 1.C
	Rated impulse voltage supply / control	0.8 kV
	Rated impulse voltage auxiliary switch	0.8 kV
	Pollution degree	3
	Environmental Conditions Operation	Class 3K23 according to IEC 60721-3-3
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-22...131°F [-30...55°C]
	Ambient temperature note	up to 140°F [60°C], max. 2 h/day
	Environmental Conditions Transport	Class 2K11 according to IEC 60721-3-2
	Transportation temperature	-40...176°F [-40...80°C]
	Environmental Conditions Storage	Class 1K21 according to IEC 60721-3-1
	Storage temperature	-22...131°F [-30...55°C]
	Servicing	maintenance-free
Weight	Weight	3.5 lb [1.6 kg]
Materials	Housing material	UL94-5VA

Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: Only possible if no (sea) water, snow, ice, sunlight, or aggressive gases directly act on the device, and if it is ensured that the ambient conditions remain within the limit values specified in the data sheet at all times.
- Only authorized specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- To calculate the torque required, the specifications supplied by the damper manufacturers concerning the cross-section and design, as well as the installation site and ventilation conditions, must be observed.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Product features

Visual status display
The device indicates its operation by means of a green LED.

Configurable Device
The factory settings cover the most common applications.
Parameters can be modified using Belimo Assistant 2, either wirelessly via Near Field Communication (NFC), or via a wired connection.

Simple direct mounting
Simple direct mounting on the damper shaft with a universal shaft clamp, supplied with an anti-rotation mechanism to prevent the actuator from rotating.

Manual override
Manual override possible with lateral handle (the gear train is disengaged for as long as the handle is actuated or remains locked).
Manual override with stationary actuator is used for installation, commissioning and maintenance of the application.

Product features

Adjustable angle of rotation
Adjustable angle of rotation with electrical end stops. The setting of the control range (Min – Max) is made with Belimo Assistant 2.

For applications with mechanical end stops or an actual operating range of less than 95°, the control range must be adjusted or an adaptation carried out using Belimo Assistant 2.

High functional reliability
The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

Innovative motorization
The actuator uses the powerful Belimo M600 microchip in combination with the INFORM method. It provides the full starting torque from a standstill with high precision (sensorless INFORM-Drive by Prof. Schrödl).


Adaptation
An adaptation can be triggered with Belimo Assistant 2. During adaptation of a mounted actuator, both damper end stops on the system are detected (entire setting range).

The actuator then moves into the position defined by the control signal.

Flexible signaling
The actuator is equipped with two adjustable auxiliary switches (locking relay) to display the damper end positions. S1 and S2 are closed when the value is lower than the configured switching point (2...98%). S4 and S5 are closed when the value is higher than the configured switching point (2...98%).

Adjustment is done with Belimo Assistant 2.

Connection
The cable can be plugged in and unplugged from the device.



Accessories

Tools

Description	Type
Service tool for wired and wireless setup, on-site operation and troubleshooting.	Belimo Assistant 2
Belimo Assistant Link Bluetooth and USB to NFC and MP-Bus converter for configurable and communicative devices	LINK.10
Connecting cable 16 ft [5 m], A: RJ11 6/4 LINK.10, B: free wire end for connection to MP/PP terminal	ZK2-GEN

Electrical accessories

Description	Type
Connecting terminal compl. for 24 V applications, with 1/2" NPT conduit connector	A.EIST.12
Connecting cable for 24 V applications, 3 ft. [1 m] Plenum, 3x 0.5 mm²/ 20 AWG, with 1/2" NPT conduit connector	A.EISC.15
Cable conduit connector, 1/2" NPT	S.EISCC.10
Connecting terminal compl. 24 V	S.EIST.10
Blind plug	S.EISBP.10

Mechanical accessories

Description	Type
Position indicator	S.MISPI.10
Baseplate extension for GM..A to GM..	Z-GMA
Mounting kit for linkage operation for flat installation	ZG-GMA
	ZG-JSA-1

Electrical installation


Supply from isolating transformer.


Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.

The cable cross-section (mm²) must be determined on the basis of the actuator performance data (VA, W), the cable resistance, the number of actuators, and the total cable length according to electrotechnical principles. High voltage drops across the installation cables can affect the function of the actuator if, for example, the nominal voltage range (AC/DC) is not respected.

Wire colors:
1 = black
2 = red
3 = white
5 = orange
S1 = violet
S2 = red
S4 = orange
S5 = pink


AC/DC 24 V, on/off






1	2	3	cw	ccw
			0°	90°
			90°	0°
			90°	0°

Auxiliary switch



Operating controls and indicators



1 Manual override lever
Rotate lever counterclockwise to end position:
- Gear train disengages, manual override possible

Return lever clockwise to starting position:
- Gear train engages, followed by standard mode

2 Status display, LED green

LED on:	operation OK
LED flashing:	Connect device with Belimo Assistant 2 for additional information
LED off:	No power supply

3 NFC interface

A Port A, see Electrical Installation

B Port B, see Electrical Installation

Service


Using Belimo Assistant 2, device parameters can be modified. Belimo Assistant 2 can operate on a smartphone, tablet, or PC. The available connection options vary depending on the hardware on which Belimo Assistant 2 is installed.


For more information about Belimo Assistant 2, refer to the Quick Guide – Belimo Assistant 2.

Wireless connection

Belimo devices marked with the NFC logo can be accessed either directly with an NFC-capable smartphone or with a Bluetooth-capable smartphone connected to Belimo Assistant Link or ZIP-BT-NFC.

Align the NFC-capable smartphone or Belimo Assistant Link with the device's NFC logo so that both NFC antennas are superposed.







Service

Wired connection

Belimo devices can be accessed by connecting Belimo Assistant Link to the USB port on a PC or laptop and to the service socket or MP-Bus wire on the device.


Belimo Assistant 2 acts as MP client. Therefore, no other MP client shall be connected to the device.







Dimensions


Shaft length

	Min. 2.05" [52 mm]
	Min. 0.75" [20 mm]

Clamping range







Further documentation

- Quick Guide – Belimo Assistant 2

Technical data sheet GMC120S.27

Damper actuator for adjusting dampers in technical building installations

- Torque motor 40 Nm
- Nominal voltage AC 100...240 V
- Control On/Off, Floating point
- Running Time (Motor) 35 s (35...150 s)
- With two integrated auxiliary switches
- With pluggable connecting cable
- 5-year warranty
- UL Listed device



Picture may differ from product

Technical data

Electrical data	Nominal voltage	AC 100...240 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 85...265 V
	Power consumption in operation	5.5 W @ 35 s
	Power consumption in rest position	0.5 W
	Transformer sizing	13 VA @ 35 s
	Auxiliary switch	2x SPST (Single Pole, Single Throw)
	Switching capacity auxiliary switch	1 mA...0.2 A, AC 30...250 V
	Switching points auxiliary switch	S1/S2: 10% / S4/S5: 90% (configurable with Belimo Assistant 2)
	Connection supply/control	Cable FRNC (halogen-free) 3 ft. [1 m] 3x 0.75 mm² [19 AWG] with 1/2" NPT conduit connector
	Connection auxiliary switch	Cable FRNC (halogen-free) 3 ft. [1 m] 4x 0.75 mm² [19 AWG] with 1/2" NPT conduit connector
	Parallel operation	See Electrical Installation or contact your local Belimo representative
Functional data	Torque motor	40 Nm
	Direction of motion motor	clockwise rotation (cw)
	Direction of motion note	selectable with Belimo Assistant 2
	Manual override	with lateral handle, can be locked
	Angle of rotation	Max. 95°
	Angle of rotation note	can be electronically limited on both sides with Belimo Assistant 2
	Running Time (Motor)	35 s / 90°
	Running time motor variable	35...150 s
	Sound power level motor	60 dB(A) @ 35 s
	Mechanical interface	Universal shaft clamp reversible 0.47...1.05" [12...26.7 mm]
	Position indication	Mechanical, pluggable
Safety data	Protection class IEC/EN	II, reinforced insulation
	Protection class UL	II, reinforced insulation
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 2
	Housing	UL Enclosure Type 2
	EMC	CE according to 2014/30/EU
	Low voltage directive	CE according to 2014/35/EU
	Certification IEC/EN	IEC/EN 60730-1 and IEC/EN 60730-2-14

Technical data

Safety data	UL Approval	cULus according to UL60730-1, UL60730-2-14 and CAN/CSA E60730-1
	UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC
	Type of action	Type 1.C
	Rated impulse voltage supply / control	2.5 kV
	Rated impulse voltage auxiliary switch	2.5 kV
	Pollution degree	3
	Environmental Conditions Operation	Class 3K23 according to IEC 60721-3-3
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-22...131°F [-30...55°C]
	Ambient temperature note	up to 140°F [60°C], max. 2 h/day
	Environmental Conditions Transport	Class 2K11 according to IEC 60721-3-2
	Transportation temperature	-40...176°F [-40...80°C]
	Environmental Conditions Storage	Class 1K21 according to IEC 60721-3-1
	Storage temperature	-22...131°F [-30...55°C]
	Servicing	maintenance-free
Weight	Weight	3.5 lb [1.6 kg]
Materials	Housing material	UL94-5VA

Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: Only possible if no (sea) water, snow, ice, sunlight, or aggressive gases directly act on the device, and if it is ensured that the ambient conditions remain within the limit values specified in the data sheet at all times.
- Caution: Line voltage!
- Only authorized specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- To calculate the torque required, the specifications supplied by the damper manufacturers concerning the cross-section and design, as well as the installation site and ventilation conditions, must be observed.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Product features

Visual status display The device indicates its operation by means of a green LED.

Configurable Device The factory settings cover the most common applications.

Parameters can be modified wireless via NFC (Near Field Communication) using Belimo Assistant 2.

Simple direct mounting Simple direct mounting on the damper shaft with a universal shaft clamp, supplied with an anti-rotation mechanism to prevent the actuator from rotating.

Manual override Manual override possible with lateral handle (the gear train is disengaged for as long as the handle is actuated or remains locked).

Manual override with stationary actuator is used for installation, commissioning and maintenance of the application.

Product features

Adjustable angle of rotation
Adjustable angle of rotation with electrical end stops. The setting of the control range (Min – Max) is made with Belimo Assistant 2.

For applications with mechanical end stops or an actual operating range of less than 95°, the control range must be adjusted or an adaptation carried out using Belimo Assistant 2.

High functional reliability
The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

Innovative motorization
The actuator uses the powerful Belimo M600 microchip in combination with the INFORM method. It provides the full starting torque from a standstill with high precision (sensorless INFORM-Drive by Prof. Schrödl).


Adaptation
An adaptation can be triggered with Belimo Assistant 2. During adaptation of a mounted actuator, both damper end stops on the system are detected (entire setting range).

The actuator then moves into the position defined by the control signal.

Flexible signaling
The actuator is equipped with two adjustable auxiliary switches (locking relay) to display the damper end positions. S1 and S2 are closed when the value is lower than the configured switching point (2...98%). S4 and S5 are closed when the value is higher than the configured switching point (2...98%).

Adjustment is done with Belimo Assistant 2.

Connection
The cable can be plugged in and unplugged from the device.



Accessories

Tools

Description	Type
Service tool for wired and wireless setup, on-site operation and troubleshooting.	Belimo Assistant 2
Belimo Assistant Link Bluetooth and USB to NFC and MP-Bus converter for configurable and communicative devices	LINK.10
Connecting cable 16 ft [5 m], A: RJ11 6/4 LINK.10, B: free wire end for connection to MP/PP terminal	ZK2-GEN

Electrical accessories

Description	Type
Connecting terminal compl. for applications with mains voltage, with 1/2" NPT conduit connector	A.EIST.15
Cable conduit connector, 1/2" NPT	S.EISCC.10
Connecting terminal compl. 100...240 V	S.EIST.11
Blind plug	S.EISBP.10

Mechanical accessories

Description	Type
Position indicator	S.MISPI.10
Baseplate extension for GM..A to GM..	Z-GMA
Mounting kit for linkage operation for flat installation	ZG-GMA ZG-JSA-1

Electrical installation


Caution: Line voltage!

Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.


The cable cross-section (mm²) must be determined on the basis of the actuator performance data (VA, W), the cable resistance, the number of actuators, and the total cable length according to electrotechnical principles. High voltage drops across the installation cables can affect the function of the actuator if, for example, the nominal voltage range (AC/DC) is not respected.


Wire colors:
1 = blue
2 = brown
3 = white
S1 = violet
S2 = red
S4 = orange
S5 = pink

AC 100...240 V, on/off




AC 100...240 V, floating point






1	2	3	cw	ccw
			0°	90°
			90°	0°
			90°	0°

Auxiliary switch



Operating controls and indicators



1 Manual override lever
Rotate lever counterclockwise to end position:
- Gear train disengages, manual override possible

Return lever clockwise to starting position:
- Gear train engages, followed by standard mode

2 Status display, LED green

LED on:	operation OK
LED flashing:	Connect device with Belimo Assistant 2 for additional information
LED off:	No power supply

3 NFC interface

A Port A, see Electrical Installation

B Port B, see Electrical Installation

Service


Using Belimo Assistant 2, device parameters can be modified. Belimo Assistant 2 can operate on a smartphone, tablet, or PC. The available connection options vary depending on the hardware on which Belimo Assistant 2 is installed.


For more information about Belimo Assistant 2, refer to the Quick Guide – Belimo Assistant 2.

Wireless connection

Belimo devices marked with the NFC logo can be accessed either directly with an NFC-capable smartphone or with a Bluetooth-capable smartphone connected to Belimo Assistant Link or ZIP-BT-NFC.


Align the NFC-capable smartphone or Belimo Assistant Link with the device's NFC logo so that both NFC antennas are superposed.







Dimensions

Shaft length

	Min. 2.05" [52 mm]
	Min. 0.75" [20 mm]

Clamping range





Further documentation

• Quick Guide – Belimo Assistant 2